



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



WPS40 400W HPS Wal-Pak Borosilicate Glass Hinged/Removab *Cooper Lighting Solutions*

| | |
|------------------|--|
| Catalog Number | WPS40 |
| Manufacturer | Cooper Lighting Solutions |
| Description | Wal-Pak 400W HPS Multi-Tap Borosilicate Glass Wall Mount, W/Lamp Bronze, Hinged Removable Door |
| Weight per unit | 22.8 (lbs/each) |
| Product Category | Lighting |

Features

| | |
|-----------------|----------------------|
| amperage rating | 1.444 |
| Ballast Type | Electronic Ballast |
| Lamp Included | True |
| Lamp Type | HIGH PRESSURE SODIUM |
| Material | Aluminum Die-Cast |
| Number of Lamps | 1 |
| Voltage Rating | 120-277V |
| Wattage | 400 |

Material, Color, and Finish

| | |
|-------|---------|
| Style | (blank) |
|-------|---------|

Descriptions

| | |
|------------------------|--|
| Description | 400W HPS WAL-PAK BOROSILICATE GLASS HINGED/REMOVAB |
| extra long description | CLS WPS40 400W HPS MT PRISM GLASS L |
| Long Description | Wal-Pak 400W HPS Multi-Tap Borosilicate Glass Wall Mount, w/Lamp Bronze, Hinged Removable Door |
| Product Type | 400W HPS MT Prism Glass Lens LMP BRZ |
| Special Features | Rugged die-cast aluminum housing and door in bronze powder-coat paint |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Cooper Lumark |
| GTIN | 00080083541232 |
| Manufacturers Part Number | WPS40 |
| UPC | 080083541232 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|----------------------|
| Category Description | Outdoor HID Lighting |
| Type | WALL MOUNT |

Packaging

| | |
|-----------------|---------|
| Carton | 1 |
| Weight Per each | 22.7999 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

| | |
|----------------------|---|
| Application | lighting |
| Mounting standard | WALL MOUNT 40 Degree C Ambient Temperature Rating;ARRA Compliant;BAA Compliant;DLC Premium;EISA Compliant;IP66 Rated;LM79/LM80 Compliant;Title 20 Compliant;UL/cUL Listed - Wet Location |