



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## WWCTD Tan Winged Wire Connector

*Nsi Industries*

Catalog Number	WWCTD
Manufacturer	Nsi Industries
Description	The Easy-Twist WWC-T-D Bulk 30, 000-Count Fibre Drum Of Tan Winged Wire Connectors Are Designed For Use On Copper Wires In The 22-10 Awg Size Range. Theyâ€™re Made Of Flame-Retardant Thermoplastic Rated For A Maximum Temperature Of 105Ëš Celsius (221Ëš Fahrenheit). The Quick-Grip Square Spring Design Grips In Fewer Twists and Can Dead-End A Single Wire, While The Ergonomic Swept-Back Wing Design and Ribbed Texture Makes Them Easy to Twist. Their Compact Design Is Useful For Applications In Tight Areas or An
Weight per unit	115.8 (lbs/each)
Product Category	Electrical Fixture Conn ( Nuts

### Features

Number of Conductors	1
Voltage Rating	600 V
Warranty	1 YEAR
Wire Type	CU Wire Only

### Material, Color, and Finish

Finish	Thermoplastic
--------	---------------



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

Description	TAN WINGED WIRE CONNECTOR
extra long description	NSI WWC-T-D WW Rubber Mastic Tape 2
Features	Connecting wires is faster and easier than ever with the professional performance features of Easy-Twist wire connectors from NSI. These connectors feature a specialized design to install in half the time of a typical wire connector, saving you time and energy. The conical screw shape grips in fewer twists and the outside of the connector is textured with easy-grip ribs for comfortable twisting. The expert team at NSI designed these connectors with key convenience and performance features for electrical in
Long Description	The Easy-Twist WWC-T-D Bulk 30,000-Count Fibre Drum of Tan Winged Wire Connectors are designed for use on copper wires in the 22-10 AWG size range. They are made of flame-retardant thermoplastic rated for a maximum temperature of 105°C (221°F Fahrenheit). The quick-grip square spring design grips in fewer twists and can dead-end a single wire, while the ergonomic swept-back wing design and ribbed texture makes them easy to twist. Their compact design is useful for applications in tight areas or an
Product Type	WW Rubber Mastic Tape 2 X 10 X .065

## Manufacturer Information

Brand	NSi
GTIN	00662381140067
Manufacturers Part Number	WWC-T-D
UPC	662381140067

## Taxonomies, Classifications, and Categories

Category Description	WIRE NUTS
----------------------	-----------

## Availability

minimum qty	30000
-------------	-------

## Packaging

Carton	30000
Weight Per each	115.8

## Uses, Certifications, and Standards

environmental conditions	105 C
Temperature Rating	105 C