



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## **X19 1/2IN Cond Body** *Crouse-Hinds*

Catalog Number	X19
Manufacturer	Crouse-Hinds
Description	Eaton Crouse-Hinds Series Condulet Mark 9 Conduit Outlet Body, Copper-Free Aluminum, X Shape, 1/2"
Weight per unit	0.5400 (lbs/each)
Product Category	Alum

### **Features**

connection	Threaded / Set Screw
dimensions	5.6900 IN X 1.7500 IN X 2.8900 IN

### **Material, Color, and Finish**

Finish	Untreated
--------	-----------

### **Dimensions and Weight**

Height	1-3/4
Hub Size	1/2 in
Length	5-11/16
Width	2-29/32

### **Descriptions**

Description	1/2IN COND BODY
extra long description	CRS-H X19 1/2 NPT AL X MARK 9 CNDT
Features	Mark 9 copper-free aluminum conduit bodies, covers and gaskets from Eaton's Crouse-Hinds Division are used in conduit systems to act as pull outlets for conductors being installed, provide openings for making splices and taps in conductors, make 90 degree bends in conduit runs, and provide for access to conductors for maintenance and future system changes. Mark 9 bodies are offered in seven different shapes, and they provide more room for heavier conductors.
Long Description	Eaton Crouse-Hinds series Condulet Mark 9 conduit outlet body, Copper-free aluminum, X shape, 1/2"
Product Type	1/2 NPT Al X Mark 9 CNDT Outlet Body

### **Manufacturer Information**

Brand	Eaton
GTIN	00782274745602
UPC	782274745602

### **Taxonomies, Classifications, and Categories**

Category Description	Form 9 condulets, covers & gaskets
Type	Conduit outlet body



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Weight Per each	0.54

## Uses, Certifications, and Standards

Application	Ind Facilities & Factories - Industrial Facilities/Factories - Other
Enclosure	Condulet
standard	UL 514B, CSA C22.2, FEDERAL SPECIFICATION W-C-586D