



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## WW722 3/4"X60' SLCT Vny Tape

*Nsi Industries*

Catalog Number	WW722
Manufacturer	Nsi Industries
Description	Warriorwrap WW-722 Black Vinyl Professional Electrical Tape Is Strong Enough For Demanding Environments and Highly Resistant to Abrasion and Corrosion. This Tape Is 7MIL Thick, 60FT Long and Has A Max Temperature Rating Of 176 Degrees. The Strong Adhesion Helps Stick to Uneven Surfaces and Keeps The Backing In Place. Top Breaking Strength and Elasticity Make Warriorwrap An Excellent Choice For Splicing, Insulating or Marking Wires.
Weight per unit	0.1900 (lbs/each)
Product Category	Markers & Marking Tapes

### Features

adhesion strength	22
Material	Vinyl
maximum voltage	600
Temperature Range	20° - 176°
Tensile Strength	17
Warranty	1 YEAR

### Material, Color, and Finish

Backing Material	Plasticized Polyvinyl Chloride (PVC)
Color	Black

### Dimensions and Weight

Length	60
Size	Thickness - 7mil - Length-60' - Width 3/4"
Thickness	.007
Width	.750



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

Description	3/4"X60' SLCT VNY TAPE
extra long description	NSI WW-722 Vyl Elec Tape Select 7mi
Features	Its Warrior Time. At NSI, we put our 45 years of experience in the electrical industry into WarriorWrap, electrical tape strong enough to rise to any challenge. For insulating, splicing or marking cables and wires on the jobsite, choose WarriorWrap, available in 12 colors and 3 grades of quality. That quality starts with strong adhesion to stick to uneven surfaces. But that's not all—it also features the best breaking strength around and unmatched elasticity to hold tight in residential or commercial en
Long Description	WarriorWrap WW-722 Black Vinyl Professional Electrical Tape is strong enough for demanding environments and highly resistant to abrasion and corrosion. This tape is 7mil thick, 60ft long and has a max temperature rating of 176 degrees. The strong adhesion helps stick to uneven surfaces and keeps the backing in place. Top breaking strength and elasticity make WarriorWrap an excellent choice for splicing, insulating or marking wires.
Product Type	Vyl Elec Tape Select 7MIL .75" 60FT
Special Features	Excellent Adhesion and Elasticity, All Weather Performance, High Tensile Strength, Resistant to UV, Abrasion and Corrosion, Flae-Retardant.

## Manufacturer Information

Brand	NSi
GTIN	00662381367266
Manufacturers Part Number	WW-722
UPC	662381367266

## Taxonomies, Classifications, and Categories

Category Description	TAPE
Type	Select Purpose

## Packaging

Carton	1
Package	100
Weight Per each	0.19

## Uses, Certifications, and Standards

Application	NSI
standard	UL 510