



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



WWCYD Yel Winged Wire Conn

Nsi Industries

Catalog Number	WWCYD
Manufacturer	Nsi Industries
Description	The Easy-Twist WWC-Y-D Bulk 35, 000-Count Fibre Drum Of Yellow Winged Wire Connectors Are Designed For Use On Copper Wires In The 18-10 Awg Size Range. Theyâ€™re Made Of Flame-Retardant Thermoplastic Rated For A Maximum Temperature Of 105Ëš Celsius (221Ëš Fahrenheit). The Quick-Grip Square Spring Design Grips In Fewer Twists and Can Dead-End A Single Wire, While The Ergonomic Swept-Back Wing Design and Ribbed Texture Makes Them Easy to Twist. Their Compact Design Is Useful For Applications In Tight Areas or
Weight per unit	143.8 (lbs/each)
Product Category	Electrical Fixture Conn (Nuts

Features

Material	Thermoplastic
Number of Conductors	1
Voltage Rating	600 V
Warranty	1 YEAR
Wire Type	CU Wire Only

Material, Color, and Finish

Color	Yellow
Finish	Thermoplastic

Dimensions and Weight

Size	H=1.01 - W=.717 - ID=.252
------	---------------------------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

Description	YEL WINGED WIRE CONN
extra long description	NSI WWC-Y-D WW Silicone Rubber Tape
Features	Connecting wires is faster and easier than ever with the professional performance features of Easy-Twist wire connectors from NSI. These connectors feature a specialized design to install in half the time of a typical wire connector, saving you time and energy. The conical screw shape grips in fewer twists and the outside of the connector is textured with easy-grip ribs for comfortable twisting. The expert team at NSI designed these connectors with key convenience and performance features for electrical in
Long Description	The Easy-Twist WWC-Y-D Bulk 35,000-Count Fibre Drum of Yellow Winged Wire Connectors are designed for use on copper wires in the 18-10 AWG size range. Theyâ€™re made of flame-retardant thermoplastic rated for a maximum temperature of 105Ëš Celsius (221Ëš Fahrenheit). The quick-grip square spring design grips in fewer twists and can dead-end a single wire, while the ergonomic swept-back wing design and ribbed texture makes them easy to twist. Their compact design is useful for applications in tight areas or
Product Type	WW Silicone Rubber Tape 1 X 30 X .020
Special Features	Winged Yellow Wire Connector - 35,000 Pcs Drum

Manufacturer Information

Brand	NSi
GTIN	00662381141064
Manufacturers Part Number	WWC-Y-D
sub brand	Easy Twist
UPC	662381141064

Taxonomies, Classifications, and Categories

Category Description	WIRE NUTS
Type	Winged Wire Connectors

Availability

minimum qty	35000
-------------	-------

Packaging

Carton	35000
Weight Per each	143.8



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application	Splicing Wire
environmental conditions	105 C
standard	UL 486C
Temperature Rating	105 C