



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



XB80L1 80 CFM Bath Fan/Light

Broan/Nutone LLC

Catalog Number	XB80L1
Manufacturer	Broan/Nutone LLC
Description	Bath Fan and Light, Ceiling, 1-Speed Type; 10-1/2 Inch Length X 11-3/8 Inch Width X 7-5/8 Inch Height Size; UI (Canada and Us) Approval; 120 Volt Ac 60 Hertz Voltage Rating; 0.4 Amp Current Rating; Yes Lamp Included; Led Lamp Type; 18 Watt Lamp Wattage
Weight per unit	13.7 (lbs/each)
Product Category	Exhaust Fans

Features

Air Flow Rate	80 CFM
Current Rating	0.4 Amp
Duct Shape	Round
Duct Size	4 Inch or 6 Inch Diameter
Grill Finish	White
Grill Shape	Rectangular
Grill Size	13-3/4 Inch Length x 14-1/4 Inch Width
Housing Shape	Rectangular
Lamp Included	Yes
Lamp Type	LED
Lamp Wattage	18 Watt
Sound Level	0.3 SONES
Ventilation Area	75 Square Foot
Voltage Rating	120 Volt AC 60 Hertz

Material, Color, and Finish

Grill Material	Polymeric
----------------	-----------

Dimensions and Weight

Size	10-1/2 Inch Length x 11-3/8 Inch Width x 7-5/8 Inch Height
------	--



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

Additional Information	Power Rating 7.3 Watt; Energy Efficiency 13.3 Watts per CFM (6 Inch Duct), 10.9 Watts per CFM (4 Inch Duct); Applicable Standard ASHRAE 62.2, HVI 2100, LEED
Commodity Description	Exhaust Fans
Description	80 CFM BATH FAN/LIGHT
extra long description	CEILING, 1-SPEED TYPE; 10-1/2 INCH LENGTH X 11-3/8 INCH WIDTH X 7-5/8 INCH HEIGHT SIZE; UL (CANADA AND US) APPROVAL; 120 VOLT AC 60 HERTZ VOLTAGE RATING; 0.4 AMP CURRENT RATING; YES LAMP INCLUDED; LED LAMP TYPE; 18 WATT LAMP WATTAGE; 80 CFM AIR FLOW RATE; 4 INCH OR 6 INCH DIAMETER DUCT SIZE; 0.3 SONES SOUND LEVEL; 13-3/4 INCH LENGTH X 14-1/4 INCH WIDTH GRILL SIZE; POLYMERIC GRILL MATERIAL; RECTANGULAR HOUSING SHAPE; ROUND DUCT SHAPE; RECTANGULAR GRILL SHAPE; WHITE GRILL FINISH; 75 SQUARE FOOT VENTILATION A
Long Description	BATH FAN AND LIGHT, CEILING, 1-SPEED TYPE; 10-1/2 INCH LENGTH X 11-3/8 INCH WIDTH X 7-5/8 INCH HEIGHT SIZE; UL (CANADA AND US) APPROVAL; 120 VOLT AC 60 HERTZ VOLTAGE RATING; 0.4 AMP CURRENT RATING; YES LAMP INCLUDED; LED LAMP TYPE; 18 WATT LAMP WATTAGE
Product Type	Bath Fan and Light

Manufacturer Information

Brand	BROAN
GTIN	00026715252497
Manufacturers Part Number	XB80L1
UPC	026715252497

Taxonomies, Classifications, and Categories

Category Description	FANS & HEATERS
Type	Ceiling, 1-Speed

Packaging

Carton	1
Weight Per each	13.6999

Uses, Certifications, and Standards

Approval	UL (CANADA AND US)
----------	--------------------