



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



XB80L1 80 CFM Bath Fan/Light

Broan/Nutone LLC

| | |
|------------------|--|
| Catalog Number | XB80L1 |
| Manufacturer | Broan/Nutone LLC |
| Description | Bath Fan and Light, Ceiling, 1-Speed Type; 10-1/2 Inch Length X 11-3/8 Inch Width X 7-5/8 Inch Height Size; UI (Canada and Us) Approval; 120 Volt Ac 60 Hertz Voltage Rating; 0.4 Amp Current Rating; Yes Lamp Included; Led Lamp Type; 18 Watt Lamp Wattage |
| Weight per unit | 13.7 (lbs/each) |
| Product Category | Exhaust Fans |

Features

| | |
|------------------|--|
| Air Flow Rate | 80 CFM |
| Current Rating | 0.4 Amp |
| Duct Shape | Round |
| Duct Size | 4 Inch or 6 Inch Diameter |
| Grill Finish | White |
| Grill Shape | Rectangular |
| Grill Size | 13-3/4 Inch Length x 14-1/4 Inch Width |
| Housing Shape | Rectangular |
| Lamp Included | Yes |
| Lamp Type | LED |
| Lamp Wattage | 18 Watt |
| Sound Level | 0.3 SONES |
| Ventilation Area | 75 Square Foot |
| Voltage Rating | 120 Volt AC 60 Hertz |

Material, Color, and Finish

| | |
|----------------|-----------|
| Grill Material | Polymeric |
|----------------|-----------|

Dimensions and Weight

| | |
|------|--|
| Size | 10-1/2 Inch Length x 11-3/8 Inch Width x 7-5/8 Inch Height |
|------|--|



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

| | |
|------------------------|---|
| Additional Information | Power Rating 7.3 Watt; Energy Efficiency 13.3 Watts per CFM (6 Inch Duct), 10.9 Watts per CFM (4 Inch Duct); Applicable Standard ASHRAE 62.2, HVI 2100, LEED |
| Commodity Description | Exhaust Fans |
| Description | 80 CFM BATH FAN/LIGHT |
| extra long description | CEILING, 1-SPEED TYPE; 10-1/2 INCH LENGTH X 11-3/8 INCH WIDTH X 7-5/8 INCH HEIGHT SIZE; UL (CANADA AND US) APPROVAL; 120 VOLT AC 60 HERTZ VOLTAGE RATING; 0.4 AMP CURRENT RATING; YES LAMP INCLUDED; LED LAMP TYPE; 18 WATT LAMP WATTAGE; 80 CFM AIR FLOW RATE; 4 INCH OR 6 INCH DIAMETER DUCT SIZE; 0.3 SONES SOUND LEVEL; 13-3/4 INCH LENGTH X 14-1/4 INCH WIDTH GRILL SIZE; POLYMERIC GRILL MATERIAL; RECTANGULAR HOUSING SHAPE; ROUND DUCT SHAPE; RECTANGULAR GRILL SHAPE; WHITE GRILL FINISH; 75 SQUARE FOOT VENTILATION A |
| Long Description | BATH FAN AND LIGHT, CEILING, 1-SPEED TYPE; 10-1/2 INCH LENGTH X 11-3/8 INCH WIDTH X 7-5/8 INCH HEIGHT SIZE; UL (CANADA AND US) APPROVAL; 120 VOLT AC 60 HERTZ VOLTAGE RATING; 0.4 AMP CURRENT RATING; YES LAMP INCLUDED; LED LAMP TYPE; 18 WATT LAMP WATTAGE |
| Product Type | Bath Fan and Light |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | BROAN |
| GTIN | 00026715252497 |
| Manufacturers Part Number | XB80L1 |
| UPC | 026715252497 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|------------------|
| Category Description | FANS & HEATERS |
| Type | Ceiling, 1-Speed |

Packaging

| | |
|-----------------|---------|
| Carton | 1 |
| Weight Per each | 13.6999 |

Uses, Certifications, and Standards

| | |
|----------|--------------------|
| Approval | UL (CANADA AND US) |
|----------|--------------------|