

# Eaton XBUT25D22

Catalog Number: XBUT25D22

Eaton XB IEC terminal block, Screw Connection Multi-Conductor Terminal Blocks, Gray, 12 AWG/2.5 mm<sup>2</sup> maximum wire, Four-wire



## General specifications

|                             |                             |
|-----------------------------|-----------------------------|
| <b>Product Name</b>         | <b>Catalog Number</b>       |
| Eaton XB IEC terminal block | XBUT25D22                   |
| <b>UPC</b>                  | <b>Product Length/Depth</b> |
| 782116905157                | 1.85 in                     |
| <b>Product Height</b>       | <b>Product Width</b>        |
| 2.17 in                     | 0.2 in                      |
| <b>Product Weight</b>       | <b>Warranty</b>             |
| 0.03 lb                     | 1 year                      |
| <b>Certifications</b>       |                             |
| UL Listed                   |                             |
| CSA Certified               |                             |

defaultTaxonomyAttributeLabel

## Resources

### Type

IEC-XB Series

### Amperage Rating

28A (IEC), 20A (UL)

### Voltage rating

IEC 500V, UL 150V

### Brochures

[XB IEC TERMINAL BLOCKS](#)

[XB IEC terminal blocks—versatility, quality, and reliability](#)

### Catalogs

[Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions](#)

### Specifications and datasheets

[Eaton Specification Sheet - XBUT25D22](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

# Eaton XBUT25D22

Catalog Number: XBUT25D22

Eaton XB IEC terminal block, Screw Connection Multi-Conductor Terminal Blocks, Gray, 12 AWG/2.5 mm<sup>2</sup> maximum wire, Four-wire



## General specifications

|                             |                             |
|-----------------------------|-----------------------------|
| <b>Product Name</b>         | <b>Catalog Number</b>       |
| Eaton XB IEC terminal block | XBUT25D22                   |
| <b>UPC</b>                  | <b>Product Length/Depth</b> |
| 782116905157                | 1.85 in                     |
| <b>Product Height</b>       | <b>Product Width</b>        |
| 2.17 in                     | 0.2 in                      |
| <b>Product Weight</b>       | <b>Warranty</b>             |
| 0.03 lb                     | 1 year                      |
| <b>Certifications</b>       |                             |
| UL Listed                   |                             |
| CSA Certified               |                             |

defaultTaxonomyAttributeLabel

## Resources

### Type

IEC-XB Series

### Amperage Rating

28A (IEC), 20A (UL)

### Voltage rating

IEC 500V, UL 150V

### Brochures

[XB IEC TERMINAL BLOCKS](#)

[XB IEC terminal blocks—versatility, quality, and reliability](#)

### Catalogs

[Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions](#)

### Specifications and datasheets

[Eaton Specification Sheet - XBUT25D22](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)