

Specifications



Eaton XBUT4BU

Eaton XB IEC terminal block, Screw connection single level-through-feed, Blue, 10 AWG/4 mm² maximum wire

General specifications

PRODUCT NAME	Eaton XB IEC terminal block
CATALOG NUMBER	XBUT4BU
UPC	782116894307
PRODUCT LENGTH/DEPTH	1.85 in
PRODUCT HEIGHT	2.17 in
PRODUCT WIDTH	0.24 in
PRODUCT WEIGHT	0.01 lb
WARRANTY	1 year
CERTIFICATIONS	CSA Certified UL Listed



Product specifications

TYPE	IEC-XB Series
AMPERAGE RATING	41A (IEC), 30A (EN), 38A (EN), 30A (UL)
VOLTAGE RATING	IEC 800V, EN 700V, UL 600V

Resources

SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - XBUT4BU
-------------------------------	---

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc

Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights
Reserved.

Eaton is a registered trademark.

All other trademarks are property of
their respective owners.

Follow us on social media to get the latest
product and support information.



Specifications



Eaton XBUT4BU

Eaton XB IEC terminal block, Screw connection single level-through-feed, Blue, 10 AWG/4 mm² maximum wire

General specifications

PRODUCT NAME	Eaton XB IEC terminal block
CATALOG NUMBER	XBUT4BU
UPC	782116894307
PRODUCT LENGTH/DEPTH	1.85 in
PRODUCT HEIGHT	2.17 in
PRODUCT WIDTH	0.24 in
PRODUCT WEIGHT	0.01 lb
WARRANTY	1 year
CERTIFICATIONS	CSA Certified UL Listed



Product specifications

TYPE	IEC-XB Series
AMPERAGE RATING	41A (IEC), 30A (EN), 38A (EN), 30A (UL)
VOLTAGE RATING	IEC 800V, EN 700V, UL 600V

Resources

SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - XBUT4BU
-------------------------------	---

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc

Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights
Reserved.

Eaton is a registered trademark.

All other trademarks are property of
their respective owners.

Follow us on social media to get the latest
product and support information.

