

Eaton XBUT4FBEL24

Catalog Number: XBUT4FBEL24

Eaton XB IEC terminal block, Screw Connection Fuse Terminal Blocks, for 5 x 20 mm Fuse, Black, 10 AWG/4 mm² maximum wire, With LED 12–30V, 1–2.5 mA light

General specifications



Product Name	Catalog Number
Eaton XB IEC terminal block	XBUT4FBEL24
UPC	Product Length/Depth
782116905225	1.85 in
Product Height	Product Width
2.17 in	0.24 in
Product Weight	Warranty
0.04 lb	1 year
Certifications	
CSA Certified	
UL Listed	

Product specifications

Special features

With LED 12–30V, 1–2.5 mA light

Type

IEC-XB Series

Amperage Rating

6.30A (IEC), 6.30A (UL)

Voltage rating

UL 600V

Resources

Specifications and datasheets

[Eaton Specification Sheet - XBUT4FBEL24](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

Eaton XBUT4FBEL24

Catalog Number: XBUT4FBEL24

Eaton XB IEC terminal block, Screw Connection Fuse Terminal Blocks, for 5 x 20 mm Fuse, Black, 10 AWG/4 mm² maximum wire, With LED 12–30V, 1–2.5 mA light

General specifications



Product Name	Catalog Number
Eaton XB IEC terminal block	XBUT4FBEL24
UPC	Product Length/Depth
782116905225	1.85 in
Product Height	Product Width
2.17 in	0.24 in
Product Weight	Warranty
0.04 lb	1 year
Certifications	
CSA Certified	
UL Listed	

Product specifications

Special features

With LED 12–30V, 1–2.5 mA light

Type

IEC-XB Series

Amperage Rating

6.30A (IEC), 6.30A (UL)

Voltage rating

UL 600V

Resources

Specifications and datasheets

[Eaton Specification Sheet - XBUT4FBEL24](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)