

Eaton XBUT6FBNL24

Catalog Number: XBUT6FBNL24

Eaton XB IEC terminal block, Fuse Terminal Blocks with LED 12-30V, 1-2.5 mA, Black, 8 AWG/6 mm² maximum wire

General specifications



Product Name	Catalog Number
Eaton XB IEC terminal block	XBUT6FBNL24
UPC	Product Length/Depth
782116905263	1.85 in
Product Height	Product Width
2.17 in	0.32 in
Product Weight	Warranty
0.03 lb	1 year
Certifications	Catalog Notes
UL Listed CSA Certified	As disconnect terminal block 500V, as fuse terminal block 400V.

Product specifications

Type

Screw Connection Fuse Terminal Blocks for 6.3 x 32 mm Fuse

Amperage Rating

10A (IEC), 10A (UL)

Voltage rating

UL 400V

Resources

Brochures

[XB IEC TERMINAL BLOCKS](#)

[XB IEC terminal blocks—versatility, quality, and reliability](#)

Specifications and datasheets

[Eaton Specification Sheet - XBUT6FBNL24](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

Eaton XBUT6FBNL24

Catalog Number: XBUT6FBNL24

Eaton XB IEC terminal block, Fuse Terminal Blocks with LED 12-30V, 1-2.5 mA, Black, 8 AWG/6 mm² maximum wire

General specifications



Product Name	Catalog Number
Eaton XB IEC terminal block	XBUT6FBNL24
UPC	Product Length/Depth
782116905263	1.85 in
Product Height	Product Width
2.17 in	0.32 in
Product Weight	Warranty
0.03 lb	1 year
Certifications	Catalog Notes
UL Listed CSA Certified	As disconnect terminal block 500V, as fuse terminal block 400V.

Product specifications

Type

Screw Connection Fuse Terminal Blocks for 6.3 x 32 mm Fuse

Amperage Rating

10A (IEC), 10A (UL)

Voltage rating

UL 400V

Resources

Brochures

[XB IEC TERMINAL BLOCKS](#)

[XB IEC terminal blocks—versatility, quality, and reliability](#)

Specifications and datasheets

[Eaton Specification Sheet - XBUT6FBNL24](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)