

# Eaton XBUT6FBNL250

Catalog Number: XBUT6FBNL250

Eaton XB IEC terminal block, Fuse Terminal Blocks with LED 110-250V, 0.5-2.5 mA, Black, 8 AWG/6 mm<sup>2</sup> maximum wire

## General specifications



<b>Product Name</b>	<b>Catalog Number</b>
Eaton XB IEC terminal block	XBUT6FBNL250
<b>UPC</b>	<b>Product Length/Depth</b>
782116905287	1.85 in
<b>Product Height</b>	<b>Product Width</b>
2.17 in	0.32 in
<b>Product Weight</b>	<b>Warranty</b>
0.05 lb	1 year
<b>Certifications</b>	<b>Catalog Notes</b>
UL Listed CSA Certified	As disconnect terminal block 500V, as fuse terminal block 400V.

## Product specifications

### Type

Screw Connection Fuse Terminal Blocks for 6.3 x 32 mm Fuse

### Amperage Rating

10A (IEC), 10A (UL)

### Voltage rating

UL 400V

## Resources

### Specifications and datasheets

[Eaton Specification Sheet - XBUT6FBNL250](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://Eaton.com/socialmedia)

# Eaton XBUT6FBNL250

Catalog Number: XBUT6FBNL250

Eaton XB IEC terminal block, Fuse Terminal Blocks with LED 110-250V, 0.5-2.5 mA, Black, 8 AWG/6 mm<sup>2</sup> maximum wire

## General specifications



<b>Product Name</b>	<b>Catalog Number</b>
Eaton XB IEC terminal block	XBUT6FBNL250
<b>UPC</b>	<b>Product Length/Depth</b>
782116905287	1.85 in
<b>Product Height</b>	<b>Product Width</b>
2.17 in	0.32 in
<b>Product Weight</b>	<b>Warranty</b>
0.05 lb	1 year
<b>Certifications</b>	<b>Catalog Notes</b>
UL Listed CSA Certified	As disconnect terminal block 500V, as fuse terminal block 400V.

## Product specifications

### Type

Screw Connection Fuse Terminal Blocks for 6.3 x 32 mm Fuse

### Amperage Rating

10A (IEC), 10A (UL)

### Voltage rating

UL 400V

## Resources

### Specifications and datasheets

[Eaton Specification Sheet - XBUT6FBNL250](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://Eaton.com/socialmedia)