

# Eaton XTOE005CCS

Catalog Number: XTOE005CCS

Eaton C440 electronic overload relay, XT IEC Electronic Overload Relay, 1-5A overload range, 45 mm frame, NO-NC contact configuration, Direct to contactor mounting, Selectable - 10A, 10, 20, 30 trip type

## General specifications



Photo is representative

### Product Name

Eaton C440 electronic overload relay

### Catalog Number

XTOE005CCS

### UPC

786685416465

### Product Length/Depth

1.8 in

### Product Height

4.3 in

### Product Width

1.42 in

### Product Weight

1 lb

### Compliances

CE Marked

ATEX Compliant

RoHS Compliant

### Certifications

EN 60947

UL Listed

CSA Certified

IEC 60947

## Product specifications

### Overload range

1-5A

### Type

Electronic overload relay

### Frame size

45 mm

### Mounting method

Direct

### Contact configuration

NO, NC

### Trip type

Selectable 10 A, class 10 ,20, 30

## Resources

### Brochures

[C440 Electronic Overload Relay](#)

### Specifications and datasheets

[Eaton Specification Sheet - XTOE005CCS](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

# Eaton XTOE005CCS

Catalog Number: XTOE005CCS

Eaton C440 electronic overload relay, XT IEC Electronic Overload Relay, 1-5A overload range, 45 mm frame, NO-NC contact configuration, Direct to contactor mounting, Selectable - 10A, 10, 20, 30 trip type

## General specifications



Photo is representative

### Product Name

Eaton C440 electronic overload relay

### Catalog Number

XTOE005CCS

### UPC

786685416465

### Product Length/Depth

1.8 in

### Product Height

4.3 in

### Product Width

1.42 in

### Product Weight

1 lb

### Compliances

CE Marked

ATEX Compliant

RoHS Compliant

### Certifications

EN 60947

UL Listed

CSA Certified

IEC 60947

## Product specifications

### Overload range

1-5A

### Type

Electronic overload relay

### Frame size

45 mm

### Mounting method

Direct

### Contact configuration

NO, NC

### Trip type

Selectable 10 A, class 10 ,20, 30

## Resources

### Brochures

[C440 Electronic Overload Relay](#)

### Specifications and datasheets

[Eaton Specification Sheet - XTOE005CCS](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)