



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## XTOR8B 81W Led Wallpack 50K 8502LM

*Cooper Lighting Solutions*

Catalog Number	XTOR8B
Manufacturer	Cooper Lighting Solutions
Description	Crosstour Maxx, Led 81W, Wall Mount, Full Cutoff Door, 5000K, 120-277V, Carbon Bronze
Weight per unit	12.3 (lbs/each)
Product Category	Lighting

### Features

amperage rating	0.71 (at 120V)/0.31 (at 277V)
Ballast Type	N/A
Lamp Included	Yes
Lamp Type	LED
Material	Die-Cast Aluminum
Number of Lamps	1
Socket Type	N/A
Voltage Rating	120-277V
Wattage	81 W

### Material, Color, and Finish

Finish	Carbon Bronze
Style	(blank)

### Descriptions

Description	81W LED WALLPACK 50K 8502LM
extra long description	CLS XTOR8B CBN BZ,80W,5000K,120-277
Long Description	Crosstour MAXX, LED 81W, Wall Mount, Full Cutoff Door, 5000K, 120-277V, Carbon Bronze
Product Type	CBN BZ, 80W, 5000K, 120-277V
Special Features	Wall, inverted or pole mount. Energy saving replacement up to 400W HID

### Manufacturer Information

Brand	LUMARK
GTIN	00080083774814
Manufacturers Part Number	XTOR8B
UPC	080083774814

### Taxonomies, Classifications, and Categories

Category Description	LED FLOODLIGHTS, WALLPACKS, BOLLARDS & LANDSCAPE LIGHTING
Type	WALL MOUNT



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Package	2
Weight Per each	12.3

## Uses, Certifications, and Standards

Application	lighting
Mounting	Wall/Surface Mount
standard	UL/cUL Listed - Wet Location;3G Vibration Tested;IP66 Rated;NOM Compliant;DLC Qualified;LM79/LM80 Compliant;DLC Premium;40 Degree C Ambient Temperature Rating;Dark Sky Compliant;RoHS Compliant