

Eaton XTCR009B21TD

Catalog Number: XTCR009B21TD

Eaton XT IEC contactor, 9A, 24 Vdc, 2NO-2NO, 9A, Frame B, 45 mm, 0.5, 1.5/ 3, 3, 5, 7.5 hp (1/3PH @115, 230/200, 230, 460, 575 V), Three-pole, Reversing, XT IEC series, Screw terminals, Full voltage reversing contactor

General specifications



Product Name

Eaton XT IEC contactor

Catalog Number

XTCR009B21TD

UPC

782116884896

Product Length/Depth

117 mm

Product Height

68 mm

Product Width

90 mm

Product Weight

0.28 kg

Warranty

1 year

Compliances

CE Marked

RoHS Compliant

Certifications

CSA Certified

EN 60947

UL Listed

IEC 60947

Catalog Notes

Screw terminals (6-65A); 5 mm (80-150A); no lugs (185-2000A)

defaultTaxonomyAttributeLabel

Amperage Rating

9A

HP rating - max

0.5, 1.5/ 3, 3, 5, 7.5 hp (1/3PH @115,230/200,230,460,575 V)

Number Of Poles

Three-pole

Type

Full voltage reversing contactor

Frame size

45 mm

Terminals

Screw terminals

Coil voltage

24 Vdc

Contact configuration

2 NO, 2 NO

Continuous ampere rating

9 A

Series

XT IEC

Operation

Reversing

Resources

Catalogs

[Eaton's Volume 5—Motor Control and Protection](#)

Drawings

[XTCR_B 2D Drawing Xchange](#)

[XTCR_B 3D Inventor](#)

[XTCR_B AutoCAD 2D Footprint \(mm\)](#)

[XTCR_B AutoCAD 2D Footprint](#)

[XTCR_B 2D PDF](#)

[XTCR_B 3D Model Xchange](#)

Specifications and datasheets

[Eaton Specification Sheet - XTCR009B21TD](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia

Eaton XTCR009B21TD

Catalog Number: XTCR009B21TD

Eaton XT IEC contactor, 9A, 24 Vdc, 2NO-2NO, 9A, Frame B, 45 mm, 0.5, 1.5/ 3, 3, 5, 7.5 hp (1/3PH @115, 230/200, 230, 460, 575 V), Three-pole, Reversing, XT IEC series, Screw terminals, Full voltage reversing contactor

General specifications



Product Name

Eaton XT IEC contactor

Catalog Number

XTCR009B21TD

UPC

782116884896

Product Length/Depth

117 mm

Product Height

68 mm

Product Width

90 mm

Product Weight

0.28 kg

Warranty

1 year

Compliances

CE Marked

RoHS Compliant

Certifications

CSA Certified

EN 60947

UL Listed

IEC 60947

Catalog Notes

Screw terminals (6-65A); 5 mm (80-150A); no lugs (185-2000A)

defaultTaxonomyAttributeLabel

Amperage Rating

9A

HP rating - max

0.5, 1.5/ 3, 3, 5, 7.5 hp (1/3PH @115,230/200,230,460,575 V)

Number Of Poles

Three-pole

Type

Full voltage reversing contactor

Frame size

45 mm

Terminals

Screw terminals

Coil voltage

24 Vdc

Contact configuration

2 NO, 2 NO

Continuous ampere rating

9 A

Series

XT IEC

Operation

Reversing

Resources

Catalogs

[Eaton's Volume 5—Motor Control and Protection](#)

Drawings

[XTCR_B 2D Drawing Xchange](#)

[XTCR_B 3D Inventor](#)

[XTCR_B AutoCAD 2D Footprint \(mm\)](#)

[XTCR_B AutoCAD 2D Footprint](#)

[XTCR_B 2D PDF](#)

[XTCR_B 3D Model Xchange](#)

Specifications and datasheets

[Eaton Specification Sheet - XTCR009B21TD](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia