



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



YA25A3 1/0AWG Alcu 1H Lug

Burndy LLC

Catalog Number	YA25A3
Manufacturer	Burndy LLC
Description	1/0 Awg, Al Terminal, One Hole, 3/8", Stud Size, AL9CU, Internal Chamfer, Tin Plated, Prefilled Penetrox , End Cap, UI/Csa, 90 C, Up to 35KV, Tan Color Code, 296 Die Index.
Weight per unit	0.0500 (lbs/each)
Product Category	Large Terminals & Connectors

Features

Die Index	296
Material	Aluminum
Voltage Rating	35

Material, Color, and Finish

Color Code	TAN
------------	-----

Descriptions

Description	1/0AWG ALCU 1H LUG
extra long description	BUR YA25A3 1/0 AL 1-HOLE, 3/8
Long Description	1/0 AWG, AL Terminal, One Hole, 3/8", Stud Size, AL9CU, Internal Chamfer, Tin Plated, Prefilled PENETROX , End Cap, UL/CSA, 90 C, Up to 35kV, Tan Color Code, 296 Die Index.
Product Type	Terminal
Special Features	Features: Type YA-A Aluminum Tin-Plated Compression HYLUG Terminals are dual-rated and designed for use on both aluminum and copper conductors. Designed for heavy duty application to 35kV. YA-A terminals are prefilled with PENETROX oxide inhibitor and assembled with color-coded end caps. Designed for a permanent trouble-free electrical termination. Heavy duty wall thickness provides maximum conductivity, low resistance, and ductility. Electro-Tin Plating provides durable long lasting corrosion resistance.

Manufacturer Information

Brand	BURNDY
GTIN	00781810753101
Manufacturers Part Number	YA25A3
UPC	781810753101

Taxonomies, Classifications, and Categories

Category Description	Comp & Mech Lugs and Butt Splices
Type	YA-A, Dual Rated



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Package	10
Weight Per each	0.05

Uses, Certifications, and Standards

Application	Wire Termination
standard	UL 486A-486B