



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



YA28LBOX 4/0 Cu 1H Short 1/2 Burndy LLC

Catalog Number	YA28LBOX
Manufacturer	Burndy LLC
Description	4/0 Awg Cu, One Hole, 1/2 Stud Size, Standard Barrel, Inspection Window, Internal Chamfer, Tin Plated, UI/Csa 90 Up to 35KV, Purple Color Code, 15 Die Index.
Weight per unit	0.1000 (lbs/each)
Product Category	Large Terminals & Connectors

Features

Die Index	15
Material	Copper
Voltage Rating	35

Material, Color, and Finish

Color Code	PURPLE
------------	--------

Descriptions

Description	4/0 CU 1H SHORT 1/2
extra long description	BUR YA28LBOX 4/0 CU 1-HOLE SHORT 1/2
Long Description	4/0 AWG CU, One Hole, 1/2 Stud Size, Standard Barrel, Inspection Window, Internal Chamfer, Tin Plated, UL/CSA 90 Up to 35kV, PURPLE Color Code, 15 Die Index.
Product Type	Terminal
Special Features	Features: UL Listed 90 DEG C, 600 V - 35 KV, 45 DEG And 90 DEG Angles Are Available, Wire Strip Length: 1-1/8 IN, Finish: Electro-Tin Plated, Package: Box, Temperature Rating: 90 DEG C, Die Index: 15, Tongue Angle: Straight, Color Code: Purple, Tools, Die Set Catalog Number, And (number Of Crimps): Mechanical: MD6, OUR840, MD7-34R Tool, W28VT, W28RT, X28RT Die, (2), Hydraulic: BCT500HS, Y500CTHS Tool, W28VT, W28RT Die, (2), X28RT Die, (3), Y35, Y39, Y750, PAT750 Tool, U28RT Die, (1), Y46 Tool, U28RT Die Wi

Manufacturer Information

Brand	BURNDY
GTIN	00781810554104
Manufacturers Part Number	YA28LBOX
UPC	781810554104

Taxonomies, Classifications, and Categories

Category Description	Comp & Mech Lugs and Butt Splices
Type	Standard Barrel, Tin Plated



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Package	10
Weight Per each	0.1

Uses, Certifications, and Standards

Application	Wire Termination
standard	UL 486A-486B