

# Eaton XTCE065D00C

Catalog Number: XTCE065D00C

Eaton XT IEC contactor, 65A, 415 Vac, 50 Hz, 480 Vac, 60 Hz, 0NO-0NC, 65A, Frame D, 55 mm, 50-60 Hz, 5, 10, 15/ 20, 25, 50, 60 hp (1/3PH @115, 200, 230/200, 230, 460, 575 V), Three-pole, Screw terminals, FVNR

## General specifications



Photo is representative

### Product Name

Eaton XT IEC contactor

### Catalog Number

XTCE065D00C

### UPC

782116486601

### Product Length/Depth

2.244 in

### Product Height

5.945 in

### Product Width

4.567 in

### Product Weight

2.4 lb

### Warranty

1 year

### Compliances

RoHS Compliant

CE Marked

### Certifications

UL Listed

CSA Certified

IEC 60947

EN 60947

### Catalog Notes

Screw terminals (6-65A); 5 mm (80-150A); no lugs (185-2000A)

## Product specifications

### Amperage Rating

65A

### HP rating - max

5, 10, 15/ 20, 25, 50, 60 hp (1/3PH  
@ 115,200,230/200,230,460,575 V)

### Number Of Poles

Three-pole

### Type

Full voltage non-reversing contactor

### Frequency rating

50-60 Hz

### Frame size

55 mm

### Terminals

Screw terminals

### Coil

412-480 Vac, 50/60 Hz

### Coil voltage

415-480 Vac, 50/60 Hz

### Contact configuration

0 NO, 0 NC

### Continuous ampere rating

65 A

### Series

XT IEC

### Operation

Non-reversing

## Resources

### Specifications and datasheets

[Eaton Specification Sheet - XTCE065D00C](#)

### Warranty guides

[Selling Policy 25-000 - Distribution and Control Products and Services](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

# Eaton XTCE065D00C

Catalog Number: XTCE065D00C

Eaton XT IEC contactor, 65A, 415 Vac, 50 Hz, 480 Vac, 60 Hz, 0NO-0NC, 65A, Frame D, 55 mm, 50-60 Hz, 5, 10, 15/ 20, 25, 50, 60 hp (1/3PH @115, 200, 230/200, 230, 460, 575 V), Three-pole, Screw terminals, FVNR

## General specifications



Photo is representative

### Product Name

Eaton XT IEC contactor

### Catalog Number

XTCE065D00C

### UPC

782116486601

### Product Length/Depth

2.244 in

### Product Height

5.945 in

### Product Width

4.567 in

### Product Weight

2.4 lb

### Warranty

1 year

### Compliances

RoHS Compliant

CE Marked

### Certifications

UL Listed

CSA Certified

IEC 60947

EN 60947

### Catalog Notes

Screw terminals (6-65A); 5 mm (80-150A); no lugs (185-2000A)

## Product specifications

### Amperage Rating

65A

### HP rating - max

5, 10, 15/ 20, 25, 50, 60 hp (1/3PH  
@ 115,200,230/200,230,460,575 V)

### Number Of Poles

Three-pole

### Type

Full voltage non-reversing contactor

### Frequency rating

50-60 Hz

### Frame size

55 mm

### Terminals

Screw terminals

### Coil

412-480 Vac, 50/60 Hz

### Coil voltage

415-480 Vac, 50/60 Hz

### Contact configuration

0 NO, 0 NC

### Continuous ampere rating

65 A

### Series

XT IEC

### Operation

Non-reversing

## Resources

### Specifications and datasheets

[Eaton Specification Sheet - XTCE065D00C](#)

### Warranty guides

[Selling Policy 25-000 - Distribution and Control Products and Services](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)