

# Eaton XTCE095FS1A

Catalog Number: XTCE095FS1A

Eaton XT IEC contactor, 95A, Side-mounted, 110 Vac 50 Hz, 120 Vac 60 Hz, 1NO-1NC, 95A, Frame F, 90 mm, 50-60 Hz, 40, 50, 100, 125 hp (3PH @200, 230, 460, 575 V), Three-pole, Screw terminals, Full voltage non-reversing contactor



Photo is representative

## General specifications

### Product Name

Eaton XT IEC contactor

### Catalog Number

XTCE095FS1A

### UPC

786685365145

### Product Length/Depth

1 in

### Product Height

1 in

### Product Width

1 in

### Product Weight

1 lb

### Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Certifications

UL Listed

CSA Certified

EN 60947

IEC 60947

## Product specifications

### Amperage Rating

95A

### HP rating - max

40, 50, 100, 125 hp (3PH @200,230,460,575 V)

### Number Of Poles

Three-pole

### Type

Full voltage non-reversing contactor

### Frequency rating

50-60 Hz

### Frame size

90 mm

### Terminals

Screw terminals

### Coil

110-120 Vac, 50/60 Hz

### Coil voltage

110-120 Vac, 50/60 Hz

### Contact configuration

1 NO, 1 NC

### Continuous ampere rating

95 A

### Series

XT IEC

### Operation

Non-reversing

## Resources

### Specifications and datasheets

[Eaton Specification Sheet - XTCE095FS1A](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

# Eaton XTCE095FS1A

Catalog Number: XTCE095FS1A

Eaton XT IEC contactor, 95A, Side-mounted, 110 Vac 50 Hz, 120 Vac 60 Hz, 1NO-1NC, 95A, Frame F, 90 mm, 50-60 Hz, 40, 50, 100, 125 hp (3PH @200, 230, 460, 575 V), Three-pole, Screw terminals, Full voltage non-reversing contactor



Photo is representative

## General specifications

### Product Name

Eaton XT IEC contactor

### Catalog Number

XTCE095FS1A

### UPC

786685365145

### Product Length/Depth

1 in

### Product Height

1 in

### Product Width

1 in

### Product Weight

1 lb

### Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Certifications

UL Listed

CSA Certified

EN 60947

IEC 60947

## Product specifications

### Amperage Rating

95A

### HP rating - max

40, 50, 100, 125 hp (3PH @200,230,460,575 V)

### Number Of Poles

Three-pole

### Type

Full voltage non-reversing contactor

### Frequency rating

50-60 Hz

### Frame size

90 mm

### Terminals

Screw terminals

### Coil

110-120 Vac, 50/60 Hz

### Coil voltage

110-120 Vac, 50/60 Hz

### Contact configuration

1 NO, 1 NC

### Continuous ampere rating

95 A

### Series

XT IEC

### Operation

Non-reversing

## Resources

### Specifications and datasheets

[Eaton Specification Sheet - XTCE095FS1A](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)