

**BURNDY Catalog Number**  
**UPC Number**

YAEV10  
7818100278066

**Description**

12-10 NYL. HVY DTY RING, #8-10 Stud

**Status**

Active

**Web Use**

BURNDY Product Line

**Dimensional**

Length (in) 1.16  
Tongue Type Ring  
Stud Size (in) #10,#8  
Pad Width (in) 0.37

**Electrical**

Max Voltage Rating 600

**General**

**Product Description**

Copper Terminal, Ring Tongue w/ Inspection Hole, Wire Range 12-10 AWG, #8-#10 Stud, Nylon Insulated, Short Barrel, Tin Plated, 600 Volts Max.

**Conductor(s)**

Aircraft Cable Size (Range) AN 12-AN 10  
Copper Solid Size (Range) N/A  
Navy Cable Size (Range) N/A  
Copper Stranded (Range) 12-10

**Physical**

Type of Plating Tin  
Connector Type Terminal  
Color Code Yellow  
Insulation Type Nylon  
Plated (Yes or No) Y

**Approvals / Certifications**

Industry Standards Military Specified (Mil-Spec),UL486  
UL Listed Y  
CSA Certified N  
ROHS Compatible Compliant  
UL Recognized N  
CULUS N

**Documentation**

For further technical assistance, please contact us



**BURNDY LLC - USA**

47 East Industrial Park Drive  
Manchester NH 03109

**BURNDY Technical Services**

47 East Industrial Park Drive  
Manchester NH 03109

Hours: 8:00 AM - 5:00 PM  
Monday - Friday  
Phone: 800-346-4175



**BURNDY Catalog Number** YAEV10  
**UPC Number** 7818100278066  
**Description** 12-10 NYL. HVY DTY RING, #8-10 Stud  
**Status** Active

**Web Use**  
 BURNDY Product Line

Dimensional	
Length (in)	1.16
Tongue Type	Ring
Stud Size (in)	#10,#8
Pad Width (in)	0.37

Electrical	
Max Voltage Rating	600

General	
Product Description	Copper Terminal, Ring Tongue w/ Inspection Hole, Wire Range 12-10 AWG, #8-#10 Stud, Nylon Insulated, Short Barrel, Tin Plated, 600 Volts Max.

Conductor(s)	
Aircraft Cable Size (Range)	AN 12-AN 10
Copper Solid Size (Range)	N/A
Navy Cable Size (Range)	N/A
Copper Stranded (Range)	12-10

Physical	
Type of Plating	Tin
Connector Type	Terminal
Color Code	Yellow
Insulation Type	Nylon
Plated (Yes or No)	Y

Approvals / Certifications	
Industry Standards	Military Specified (Mil-Spec),UL486
UL Listed	Y
CSA Certified	N
ROHS Compatible	Compliant
UL Recognized	N
CULUS	N

**Documentation**

For further technical assistance, please contact us

**BURNDY LLC - USA**

47 East Industrial Park Drive  
 Manchester NH 03109

**BURNDY Technical Services**

47 East Industrial Park Drive  
 Manchester NH 03109

Hours: 8:00 AM - 5:00 PM  
 Monday - Friday  
 Phone: 800-346-4175