



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## YAV10T3BOX Ring- 12- 10 Awg - Unin

Burndy LLC

Catalog Number	YAV10T3BOX
Manufacturer	Burndy LLC
Description	Copper Compression Lug, 1 Hole W/ Inspection Window, 14-10 Awg/12-10 Awg, 1/4" Stud, Short Barrel, Tin Plated, Wire Strip Length:7/16".
Weight per unit	0.0070 (lbs/each)
Product Category	Large Terminals & Connectors

### Features

Material	Copper
pallet quantity	99999

### Descriptions

Description	RING- 12- 10 AWG - UNIN
extra long description	BUR YAV10T3BOX RING- 12- 10 AWG -
Long Description	Copper Compression Lug, 1 Hole w/ Inspection Window, 14-10 AWG/12-10 AWG, 1/4" Stud, Short Barrel, Tin Plated,Wire strip length:7/16".
Product Type	Terminal
Special Features	Features: Seamless uninsulated compression heavy duty ring tongue terminal. HYLUG Type YAV is a seamless, heavy duty uninsulated compression ring tongue terminal made from pure electrolytic copper tubing for use on copper commercial (Code) cable, Type AN aircraft cable and extra flexible conductors. Its seamless design also accommodates solid conductors. Double thick tongue provides a strong connector for demanding applications requiring high reliability. Applications include: industrials, hospitals, elect

### Manufacturer Information

Brand	BURNDY
GTIN	00781810541708
Manufacturers Part Number	YAV10T3BOX
UPC	781810541708

### Taxonomies, Classifications, and Categories

Category Description	MISC FITTINGS
Type	Ring Tongue

### Packaging

Carton	1
Package	50
Weight Per each	0.007



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

Application

For Use On Copper Commercial (Code) Cable, Type AN Aircraft Cable And Extra Flexible Conductors, Industrials, Hospitals, Electric Utilities, Shipboard And Marine, Computers, Steel Mills, Mining Equipment And Other Equipment That Is Subject To Vibration Or Requiring Dependable Electrical Performance

standard

UL467