



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



YA25L4BOX 1/0AWG 1H Lug

Burndy LLC

Catalog Number	YA25L4BOX
Manufacturer	Burndy LLC
Description	Copper Compression Lug, 1 Hole W/ Inspection Window, 1/0 Awg, 3/8" Stud, Short Barrel, Tin Plated.
Weight per unit	0.0600 (lbs/each)
Product Category	Large Terminals & Connectors

Features

Die Index	12
Material	Copper
Voltage Rating	35

Material, Color, and Finish

Color Code	PINK
------------	------

Descriptions

Description	1/0AWG 1H LUG
extra long description	BUR YA25L4BOX CULUG-1/0 STR-3/8 (M1
Long Description	Copper Compression lug, 1 Hole w/ Inspection Window, 1/0 AWG, 3/8" Stud, Short Barrel, Tin Plated.
Product Type	Terminal
Special Features	Features: UL Listed 90 DEG C, 600 V To 35 KV 45 DEG, 90 DEG Angles Are Available, Tools, Die Set Catalog Number, And (number Of Crimps): MD6, OUR840, MD7-34R Mechanical: W25VT (2), W25RT (2), X25RT (2), BCT500HS, Y500CTHS Hydraulic: W25VT (2), W25RT (2), X25RT (2), W29VT (4), Y35, Y39, Y750, Y46, PAT750 Hydraulic: U25RT (1), U2CABT (1), Dieless: MY29-3 (1), MY29-11 (1), MRC840 (2), Y644HS (1), Y81KFT (1), Y81KFTMBH (1), PAT81KFT-18V (1), Wire Strip Length: 15/16 IN, Conductor Type: Commercial Stranded Copper

Manufacturer Information

Brand	BURNDY
GTIN	00781810553503
Manufacturers Part Number	YA25L4BOX
UPC	781810553503

Taxonomies, Classifications, and Categories

Category Description	Comp & Mech Lugs and Butt Splices
Type	Standard Barrel, Tin Plated



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	0.06

Uses, Certifications, and Standards

Application	Wire Termination
standard	UL 486A-486B