



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



YA44 1000 Cu 1H Long 5/8 *Burndy LLC*

Catalog Number	YA44
Manufacturer	Burndy LLC
Description	1000 Kcmil Cu, One Hole, 5/8 Stud Size, Long Barrel, Internal Chamfer, Tin Plated, UI/Csa, 90 C, Up to 35KV, White Color Code, 27 Die Index.
Weight per unit	1.2 (lbs/each)
Product Category	Tools & Testers

Features

Die Index	27
Material	Copper
Voltage Rating	35

Material, Color, and Finish

Color Code	WHITE
------------	-------

Descriptions

Description	1000 CU 1H LONG 5/8
extra long description	BUR YA44 1000 CU 1-HOLE LONG 5/8
Long Description	1000 kcmil CU, One Hole, 5/8 Stud Size, Long Barrel, Internal Chamfer, Tin Plated, UL/CSA, 90 C, Up to 35kV, WHITE Color Code, 27 Die Index.
Product Type	Terminal
Special Features	Features: UL Listed 90 DEG C, 600 V - 35 KV, 45 DEG And 90 DEG Angles Are Available, Finish: Electro-Tin Plated, Tongue Angle: Straight, Wire Strip Length: 3-1/16 IN, Die Index: 27, Temperature Rating: 90 DEG C, Color Code: White, Tools, Die Set Catalog Number, And (number Of Crimps): Hydraulic: Y46 Tool, P44RT Die, (4), Conductor Type: Commercial Stranded Copper, Dieless Tools (number Of Crimps): Y644HS Tool, (1), Y81KFT, Y81KFTMBH, PAT81KFT-18V Tool, (4)

Manufacturer Information

Brand	BURNDY
GTIN	00781810522950
Manufacturers Part Number	YA44
UPC	781810522950

Taxonomies, Classifications, and Categories

Category Description	Comp & Mech Lugs and Butt Splices
Type	Long Barrel, Tin Plated



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Package	3
Weight Per each	1.18

Uses, Certifications, and Standards

Application	Wire Termination
standard	UL 486A-486B