



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



YGHA292N 250MCM Comp Ground Tap

Burndy LLC

Catalog Number	YGHA292N
Manufacturer	Burndy LLC
Description	Copper Compression Lug, Heavy Duty, 2 Hole W/ Inspection Probe Hole, 250 Kcmil, 1/2" Stud, 1-3/4" Stud Hole Spacing, Short Barrel.
Weight per unit	0.6229 (lbs/each)
Product Category	Large Terminals & Connectors

Features

Die Index	18
Material	Copper
pallet quantity	2880

Descriptions

Description	250MCM COMP GROUND TAP
extra long description	BUR YGHA292N CU 250 HVY DUTY GRD TE
Long Description	Copper Compression Lug, Heavy Duty, 2 Hole w/ Inspection Probe Hole, 250 kcmil, 1/2" Stud, 1-3/4" Stud Hole Spacing, Short Barrel.
Product Type	Compression
Special Features	Features: Heavy Duty HYLUG Irreversible Compression Terminals Designed Not Only To Carry Short Circuit Load, But To Also Withstand High Mechanical Stress, Each Conductor Element Has An Inspection Probe Hole To Ensure Proper Cable Insertion, UL467 Listed, Acceptable For Direct Burial In Earth Or Concrete, UL486A Listed, Prefilled With PENETROX Compound And Strip Sealed, Tools, Die Set Catalog Number, And (number Of Crimps): Y35, Y39, Y750, PAT750 Tool, U31RT Die, (2), Y45 Tool, U31RT Die With PT-6515 Adapte

Manufacturer Information

Brand	BURNDY
GTIN	00781810220382
Manufacturers Part Number	YGHA292N
UPC	781810220382

Taxonomies, Classifications, and Categories

Category Description	SERVICE ENTRANCE FITTINGS: Weatherheads & Grounding Fittings & Ground Rods
Type	Terminals



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Package	10
Weight Per each	0.6229

Uses, Certifications, and Standards

Application	For Direct Burial In Earth Or Concrete, Grounding Applications
standard	UL467;UL 486A-486B;IEEE 837