




ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



YS4C #4 Comp Cu Butt Splice *Burndy LLC*

Catalog Number	YS4C
Manufacturer	Burndy LLC
Description	4 Awg Cu, Long Barrel, Internal Chamfer, Tin Plated, UI/Csa, 90 C, Up to 35KV, Gray Color Code, 8 or 346 Die Index.
Weight per unit	0.0300 (lbs/each)
Product Category	Large Terminals & Connectors

Features

Die Index	8
Material	Copper
Voltage Rating	35

Material, Color, and Finish

Color Code	GRAY
Finish	Tin-Plated

Descriptions

Description	#4 COMP CU BUTT SPLICE
extra long description	BUR YS4C BUTT SPLICE LONG 4
Long Description	4 AWG CU, Long Barrel, Internal Chamfer, Tin Plated, UL/CSA, 90 C, Up to 35kV, GRAY Color Code, 8 or 346 Die Index.
Product Type	Splice
Special Features	Features: UL Listed 90 DEG C, 600 Volts to 35 kV, Long Barrel Length: Ideal For 600 Volt Heavy Duty Applications, Also May Be Used At Higher Voltages Up To 35KV, Four (4) Center Conductor Stops: Provides A Center Wire Stop For Proper Conductor Insertion, High Pull Out Force: Provides Added Security For Much Greater Mechanical And Electrical Properties, Oil Stop: No, Dieless Tools (number Of Crimps): Y81KFT, Y81KFTMBH, PAT81KFT-18V Tool, (1), Color Code: Gray, Tapered End: No, Die Index: 8 Or 346, Tools, Di

Manufacturer Information

Brand	BURNDY
GTIN	00781810507209
Manufacturers Part Number	YS4C
UPC	781810507209

Taxonomies, Classifications, and Categories

Category Description	Comp & Mech Lugs and Butt Splices
Type	YS, Long Barrel



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Package	50
Weight Per each	0.03

Uses, Certifications, and Standards

Application	Wire Splice
standard	UL 486A-486B