



BURNDY Catalog Number
UPC Number

YAV4CL
7818108071944
4AWG HVYDTY RING 1/4
STU,1.37 IN L
Active

Description
Status

Web Use
BURNDY Product Line

Tongue Angle
Strip Length
Length (in)
Tongue Type
Pad Width (in)

Dimensional
Straight
1/2
1.37
Ring
0.55

Product Description

General
Copper Compression Lug, Ring
Tongue, 1 Hole w/ Inspection
Hole, AN-4 Flex, 1/4" Stud, Short
Barrel, Electro-Tin Plated

Aircraft Cable Size (Range)
Copper Solid Size (Range)
Navy Cable Size (Range)
Copper Stranded (Range)

Conductor(s)
AN 4
N/A
N/A
4

Type of Plating
Connector Type
Plated (Yes or No)

Physical
Tin - Electro Plated
Terminal
Y

UL Listed
CSA Certified
ROHS Compatible
UL Recognized
Mil-Spec Class Code
CULUS

Approvals / Certifications

Y
Y
Compliant
N
Class 1
N
UL467, Military Specified (Mil-Spec)

Industry Standards

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive
Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
Monday - Friday
Phone: 800-346-4175



BURNDY Catalog Number
UPC Number

YAV4CL
 7818108071944
 4AWG HVYDTY RING 1/4
 STU,1.37 IN L
 Active

Description
Status

Web Use
 BURNDY Product Line

Tongue Angle
 Strip Length
 Length (in)
 Tongue Type
 Pad Width (in)

Dimensional
 Straight
 1/2
 1.37
 Ring
 0.55

Product Description

General
 Copper Compression Lug, Ring
 Tongue, 1 Hole w/ Inspection
 Hole, AN-4 Flex, 1/4" Stud, Short
 Barrel, Electro-Tin Plated

Aircraft Cable Size (Range)
 Copper Solid Size (Range)
 Navy Cable Size (Range)
 Copper Stranded (Range)

Conductor(s)
 AN 4
 N/A
 N/A
 4

Type of Plating
 Connector Type
 Plated (Yes or No)

Physical
 Tin - Electro Plated
 Terminal
 Y

UL Listed
 CSA Certified
 ROHS Compatible
 UL Recognized
 Mil-Spec Class Code
 CULUS

Approvals / Certifications
 Y
 Y
 Compliant
 N
 Class 1
 N
 UL467, Military Specified (Mil-
 Spec)

Industry Standards

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive
 Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
 Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
 Monday - Friday
 Phone: 800-346-4175