



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



ZB124 Button Photocontrol 105-305V

Nsi Industries

Catalog Number	ZB124
Manufacturer	Nsi Industries
Description	The Tork ZB124 Button-Style Instant Response Led Photocontrol Light Sensor Provides A Simple Way to Control Residential or Commercial Exterior Lights and Appliances Based On The Ambient Light Level. Features Include The Coated Circuit Board and Weather-Resistant Casing, Long-Life Zero-Cross Technology and The Time Delay That Prevents Stray Lights or Shadows From Triggering The Control. Designed For Applications Including Landscape Lighting, Perimeter and Security Lighting, Pole Lanterns or Signage.
Weight per unit	0.2050 (lbs/each)
Product Category	Wiring Devices

Features

Material	Polycarbonate
Voltage Rating	105-305
Warranty	1 YEAR

Material, Color, and Finish

Color	Black
-------	-------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

Description	BUTTON PHOTOCONTROL 105-305V
extra long description	TORK ZB124 Zero Cross Btn Type On 1
Features	The TORK ZB124 provides professional-grade performance for a range of residential and commercial applications. This in-post push-button style photocontrol light sensor automatically detects nightfall, allowing you to run exterior lights from dusk to dawn. Use TORK photocontrols for your garage lights, landscape lighting, pole lanterns or perimeter security lights, or in commercial applications like lightposts, signage or parking lot lights. The ZB124 saves you energy and money while adding security to your
Long Description	The TORK ZB124 button-style instant response LED photocontrol light sensor provides a simple way to control residential or commercial exterior lights and appliances based on the ambient light level. Features include the coated circuit board and weather-resistant casing, long-life zero-cross technology and the time delay that prevents stray lights or shadows from triggering the control. Designed for applications including landscape lighting, perimeter and security lighting, pole lanterns or signage.
Product Type	Zero Cross BTN Type On 1.3-1.7 Off/On Ratio 1.5:1 105-305V 1

Manufacturer Information

Brand	NSi
GTIN	00786261789129
Manufacturers Part Number	ZB124
UPC	786261789129

Taxonomies, Classifications, and Categories

Category Description	Residential dimmers, motion sensors, controls, & photo cells
----------------------	--

Packaging

Carton	1
Package	6
Weight Per each	0.205