



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



YGHC29C26 3/0 Comp Ground Tap *Burndy LLC*

Catalog Number	YGHC29C26
Manufacturer	Burndy LLC
Description	Copper Compression C Connector, 3/0 Awg(STR) - 250 Kcmil, 1/2" or 5/8" Rod (Run) & 6 Awg(Sol) - 2/0 Awg(STR) (Tap).
Weight per unit	0.2200 (lbs/each)
Product Category	Large Terminals & Connectors

Features

Die Index	997
Material	Copper
pallet quantity	9250

Descriptions

Description	3/0 COMP GROUND TAP
extra long description	BUR YGHC29C26 3/0-250 TO 6-2/0 CU G
Long Description	Copper Compression C Connector, 3/0 AWG(Str) - 250 kcmil, 1/2" or 5/8" Rod (Run) & 6 AWG(Sol) - 2/0 AWG(Str) (Tap).
Product Type	Compression
Special Features	Features: Irreversible Compression Ground Tap Figure C Connectors, Accommodates All Cable Combinations From #6 AWG Solid Through 500 KCMIL, C- Shaped Opening Permits Placing Two Continuous Parallel Cables Into Conductor Groove, UL467 Listed, Acceptable For Direct Burial In Earth Or Concrete, Prefilled With PENETROX Compound And Strip Sealed, Certain Sizes Are Also UL467 Listed And CSA Certified For Wire To Ground Rod, Tools, Die Set Catalog Number, And (number Of Crimps): HYPRESS: Y35, Y39, Y750, PAT750 To

Manufacturer Information

Brand	BURNDY
GTIN	00781810221044
Manufacturers Part Number	YGHC29C26
UPC	781810221044

Taxonomies, Classifications, and Categories

Category Description	SERVICE ENTRANCE FITTINGS: Weatherheads & Grounding Fittings & Ground Rods
Type	Taps

Packaging

Carton	1
Package	25
Weight Per each	0.22



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application	For Direct Burial Cables
standard	Direct Burial