



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



YGHC29C29 3/0-250 to 3/0-250 Ground C Burndy LLC

Catalog Number	YGHC29C29
Manufacturer	Burndy LLC
Description	Copper Compression C Connector, 3/0 Awg(STR) - 250 Kcmil, 1/2" or 5/8" Rod (Run) & 3/0 Awg(STR) - 250 Kcmil (Tap).
Weight per unit	0.2460 (lbs/each)
Product Category	Large Terminals & Connectors

Features

Die Index	997
Material	Copper
pallet quantity	7400

Descriptions

Description	3/0-250 TO 3/0-250 GROUND C
extra long description	BUR YGHC29C29 3/0-250 TO 3/0-250 GR
Long Description	Copper Compression C Connector, 3/0 AWG(Str) - 250 kcmil, 1/2" or 5/8" Rod (Run) & 3/0 AWG(Str) - 250 kcmil (Tap).
Product Type	Compression
Special Features	Features: Irreversible Compression Ground Tap Figure C Connectors, Accommodates All Cable Combinations From #6 AWG Solid Through 500 KCMIL, C- Shaped Opening Permits Placing Two Continuous Parallel Cables Into Conductor Groove, UL467 Listed, Acceptable For Direct Burial In Earth Or Concrete, Prefilled With PENETROX Compound And Strip Sealed, Certain Sizes Are Also UL467 Listed And CSA Certified For Wire To Ground Rod, Conductor Size (tap - Mm): 95 - 120 SQ-MM, Ground Rod Size: 1/2 - 5/8 IN, Tools, Die Set

Manufacturer Information

Brand	BURNDY
GTIN	00781810221051
Manufacturers Part Number	YGHC29C29
UPC	781810221051

Taxonomies, Classifications, and Categories

Category Description	SERVICE ENTRANCE FITTINGS: Weatherheads & Grounding Fittings & Ground Rods
Type	Taps

Packaging

Carton	1
Package	25
Weight Per each	0.246



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application	For Direct Burial Cables
standard	Direct Burial