



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## ZTL124 TRNLCK Adv Elec Led 105-305V

*Nsi Industries*

|                  |  |
|------------------|--|
| Catalog Number   | ZTL124   |
| Manufacturer     | Nsi Industries   |
| Description      | The Tork ZTL124 Turn-Lock Advanced Led Photocontrol Light Sensor Provides A Simple Way to Control Residential or Commercial Exterior Lights and Appliances Based On The Ambient Light Level. Features Include The Zero-Cross Switching Technology, Enhanced Surge Protection, Silicone Sensor Designed For Human Eye Response and The Coated, Weather-Resistant Circuit Board. Designed For Applications Including Led, CFL, Induction, HPS and Hid Lighting Fixtures In Roadways, Parking Lots, and Security or Flood Lights. |
| Weight per unit  | 0.2660 (lbs/each)  |
| Product Category | Lighting Photocells  |

### Features

|                       |  |
|-----------------------|--|
| action                | Twist-Lock                                       |
| Base                  | Polypropylene                                    |
| Contact Configuration | Prong  |
| Contact Rating        | 105-305  |
| Number of Pins        | 3  |
| Poles                 | 1  |
| Timing Range          | Turn On Is 1.5fc - Off-On Ratio Is 1.5:1 Average |

### Dimensions and Weight

|      |                   |
|------|-------------------|
| Size | H=2.187 - W=3.187 |
|------|-------------------|



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

|                        |   |
|------------------------|---|
| Description            | TRNLCK ADV ELEC LED 105-305V  |
| extra long description | TORK ZTL124 TurnLock LED Zero Cross   |
| Features               | The TORK ZTL124 provides professional-grade performance for commercial applications. This turn-lock LED photocontrol light sensor automatically detects nightfall, allowing you to run exterior lights from dusk to dawn. Use TORK photocontrols for a wide range of professional applications including streetlights, roadway or parking lot lights, floodlights, security lights, or any other LED luminaries. The ZTL124 saves you energy and money while adding security to your property at night. Our new zero-cross phot |
| Long Description       | The TORK ZTL124 turn-lock advanced LED photocontrol light sensor provides a simple way to control residential or commercial exterior lights and appliances based on the ambient light level. Features include the zero-cross switching technology, enhanced surge protection, silicone sensor designed for human eye response and the coated, weather-resistant circuit board. Designed for applications including LED, CFL, Induction, HPS and HID lighting fixtures in roadways, parking lots, and security or flood lights.  |
| Product Type           | Turnlock Led Zero Cross 105-305V Fail On  |
| Special Features       | 510 Joule MOV (Metal Oxide Varistor) Surge Arrestor - Locking Prongs - Molded Sealed IR Filtered Sensor   |

## Manufacturer Information

|                           |                |
|---------------------------|----------------|
| Brand                     | NSi            |
| GTIN                      | 00786261789099 |
| Manufacturers Part Number | ZTL124         |
| UPC                       | 786261789099   |

## Taxonomies, Classifications, and Categories

|                      |   |
|----------------------|---|
| Category Description | Commercial dimmers, motion sensors, & photo cells |
| Type                 | Zero Cross Turn Lock                              |

## Packaging

|                 |       |
|-----------------|-------|
| Carton          | 1     |
| Weight Per each | 0.266 |



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

|                          |               |
|--------------------------|---------------|
| Application              | NSI           |
| Enclosure                | Polypropylene |
| environmental conditions | -40 to + 140  |
| Frequency Rating         | 50-60 Hz      |
| Mounting                 | Twist-Lock    |
| Operating Temperature    | -40 to + 140  |
| standard                 | cULus         |