




GE
Lighting

66649 - F34/CW/C/WM/ECO

F34/CW/C/WM/ECO-LFL - 30PK WITH UPC STICKERS ON L



GENERAL CHARACTERISTICS

Lamp Type	Linear Fluorescent - Straight
Bulb	Linear
Base	T12
Rated Life	Medium Bi-Pin (G13)
Bulb Material	15000.0 hrs
Starting Temperature (MIN)	Sodalime glass
LEED-EB MR Credit	15.0 °C
Primary Application	222 picograms Hg per mean lumen hour
	Energy Saving

PHOTOMETRIC CHARACTERISTICS

Initial Lumens	1800.0
Mean Lumens	1500.0
Nominal Initial Lumens per Watt	52
Color Temperature	4100.0 K
Color Rendering Index (CRI)	87.0

ELECTRICAL CHARACTERISTICS

Wattage	34.0
---------	------

DIMENSIONS

Maximum Overall Length (MOL)	48.0000 in(1219.2 mm)
Nominal Length	48.000 in(1219.2 mm)
Bulb Diameter (DIA)	1.500 in(38.1 mm)

PRODUCT INFORMATION


Product Code	66649
Description	F34/CW/C/WM/ECO
Standard Package	Case
Standard Package GTIN	10043168666494
Standard Package Quantity	30
Sales Unit	Unit
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	30
UPC	043168666497



GE
Lighting

66649 - F34/CW/C/WM/ECO

F34/CW/C/WM/ECO-LFL - 30PK WITH UPC STICKERS ON L



GENERAL CHARACTERISTICS

Lamp Type	Linear Fluorescent - Straight
Bulb	Linear
Base	T12
Rated Life	Medium Bi-Pin (G13)
Bulb Material	15000.0 hrs
Starting Temperature (MIN)	Sodalime glass
LEED-EB MR Credit	15.0 °C
Primary Application	222 picograms Hg per mean lumen hour
	Energy Saving

PHOTOMETRIC CHARACTERISTICS

Initial Lumens	1800.0
Mean Lumens	1500.0
Nominal Initial Lumens per Watt	52
Color Temperature	4100.0 K
Color Rendering Index (CRI)	87.0

ELECTRICAL CHARACTERISTICS

Wattage	34.0
---------	------

DIMENSIONS

Maximum Overall Length (MOL)	48.0000 in(1219.2 mm)
Nominal Length	48.000 in(1219.2 mm)
Bulb Diameter (DIA)	1.500 in(38.1 mm)

PRODUCT INFORMATION

Product Code	66649
Description	F34/CW/C/WM/ECO
Standard Package	Case
Standard Package GTIN	10043168666494
Standard Package Quantity	30
Sales Unit	Unit
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	30
UPC	043168666497