



Fibrelyte™ meter boxes are engineered to achieve a great strength-to-weight ratio. This durable composite material is ideal for turf and walkway applications. Fibrelyte boxes achieve greater load capacity than similar plastic sizes.



Body: Polymer Composite  
Cover: Polymer Composite




**A. Polymer Composite Cover**

- Lightweight, durable Fibrelyte composite material features durable slip resistant cover design.
- Polymer concrete and steel cover options are available.
- Flush style covers are available with S. Steel Hex, Penta, or Vandal Proof hardware.

**B. Polymer Composite Body**

- Light weight, impact resistant, sloped wall body design provides increased internal volume.
- Fibrelyte body provides easy access.
- Uses standard hole saw blade (no diamond tipped carbide blades required).



| Material  | Model | Size (LxW) | Shape | Wall Type | Depths          | Design Load | Tier   |
|-----------|-------|------------|-------|-----------|-----------------|-------------|--------|
| Composite | FL08  | 9" Dia     | ○     | Straight  | 12"             | 8,000 lbf   | Tier 8 |
|           | FL09  | 10" x 15"  | □     | Flared ▽  | 12"             |             |        |
|           | FL12  | 11" x 18"  | □     | Straight  | 12"             |             |        |
|           | FL30  | 13" x 24"  | □     | Flared ▽  | 12" 18" 20" 24" |             |        |
|           | FL36  | 17" x 30"  | □     |           | 12" 18" 20" 24" |             |        |

Actual load rating is determined by the box and cover combination.



## Components and Options



**LOAD RATING**  
Medium Duty  
Non-deliberate Traffic

### STRENGTH AND DURABILITY

Superior load capacity in a lightweight, easy-to-handle material

### SECURE

Lock options available

### VARIETY OF SIZES

Round and rectangle Enclosures in many sizes and depths



**SLIP RESISTANT TEXTURE**  
and flush lid designs, allow installation in designated walkways



**AMR FRIENDLY**  
material allows accurate transmission of data

### CUSTOMIZABLE

- Color choices of green, grey and purple
- Material is easy to modify in the field with a simple hole saw

### MOUSEHOLES

ready-to-cut as needed


## Testing and Features



Tier Certified



Maximized Strength




Impact Tested




Freeze/Thaw Resilient




Security



Custom Options



Sunlight Resistant



Storage Inside



Open Bottom



Non-Flammable



Chemical Resistant



Non-Conductive

877-250-5139 | [OPI-Water@oldcastle.com](mailto:OPI-Water@oldcastle.com)

[oldcastleprecast.com/enclosuresolutions](http://oldcastleprecast.com/enclosuresolutions)



Fibrelyte™ meter boxes are engineered to achieve a great strength-to-weight ratio. This durable composite material is ideal for turf and walkway applications. Fibrelyte boxes achieve greater load capacity than similar plastic sizes.



Body: Polymer Composite  
Cover: Polymer Composite




**A. Polymer Composite Cover**

- Lightweight, durable Fibrelyte composite material features durable slip resistant cover design.
- Polymer concrete and steel cover options are available.
- Flush style covers are available with S. Steel Hex, Penta, or Vandal Proof hardware.

**B. Polymer Composite Body**

- Light weight, impact resistant, sloped wall body design provides increased internal volume.
- Fibrelyte body provides easy access.
- Uses standard hole saw blade (no diamond tipped carbide blades required).



| Material  | Model | Size (LxW) | Shape | Wall Type | Depths          | Design Load | Tier   |
|-----------|-------|------------|-------|-----------|-----------------|-------------|--------|
| Composite | FL08  | 9" Dia     | ○     | Straight  | 12"             | 8,000 lbf   | Tier 8 |
|           | FL09  | 10" x 15"  | □     | Flared    | 12"             |             |        |
|           | FL12  | 11" x 18"  | □     | Straight  | 12"             |             |        |
|           | FL30  | 13" x 24"  | □     | Flared    | 12" 18" 20" 24" |             |        |
|           | FL36  | 17" x 30"  | □     |           | 12" 18" 20" 24" |             |        |

Actual load rating is determined by the box and cover combination.



## Components and Options



**LOAD RATING**  
Medium Duty  
Non-deliberate Traffic

### STRENGTH AND DURABILITY

Superior load capacity in a lightweight, easy-to-handle material

### SECURE

Lock options available

### VARIETY OF SIZES

Round and rectangle Enclosures in many sizes and depths



**SLIP RESISTANT TEXTURE**  
and flush lid designs, allow installation in designated walkways

**AMR FRIENDLY**  
material allows accurate transmission of data

### CUSTOMIZABLE

- Color choices of green, grey and purple
- Material is easy to modify in the field with a simple hole saw


## Testing and Features



Tier Certified



Maximized Strength




Impact Tested




Freeze/Thaw Resilient



Security



Custom Options



Sunlight Resistant



Storage Inside



Open Bottom



Non-Flammable



Chemical Resistant



Non-Conductive

877-250-5139 | [OPI-Water@oldcastle.com](mailto:OPI-Water@oldcastle.com)

[oldcastleprecast.com/enclosuresolutions](http://oldcastleprecast.com/enclosuresolutions)