



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



10250T714R RD 2POS Push/Pull 1NO/1NC Class I Div 2 Eaton Corp

Catalog Number	10250T714R
Manufacturer	Eaton Corp
Description	10250T, 30.5 MM, Class I Division 2, 40 MM, Nema 3, 3R, 4, 4X, 12, 13, Nec Class I Division 2, Groups B, C and D, Non-Illuminated, Two-Position, Maintained Push and Pull, Standard, Red Actuator, Plastic Bus, 1NO-1NC
Weight per unit	0.4000 (lbs/each)
Product Category	Push Button Complete Assemble

Features

action	Red
actuator	Standard
Contact Configuration	1 NO-1 NC
media	Yes

Dimensions and Weight

Depth	1
Height	1
Size	40 mm
Width	1

Descriptions

Description	RD 2POS PUSH/PULL 1NO/1NC CLASS I DIV 2
extra long description	ETN 10250T714R Rd 2Pos Push/Pull 1N
Features	Eaton's 10250T line of 30.5 mm pushbuttons features a heavy-duty zinc die cast construction. Reliability nibs improve contact reliability even under dry circuit and fine dust conditions. In addition, drainage holes prevent the buildup of liquid inside the operator, which can prevent operation in freezing environments.
Long Description	10250T, 30.5 mm, Class I Division 2, 40 mm, NEMA 3, 3R, 4, 4X, 12, 13, NEC Class I Division 2, Groups B, C and D, Non-illuminated, Two-position, Maintained push and pull, Standard, Red actuator, Plastic bus, 1NO-1NC
Product Type	RD 2POS Push/Pull 1NO/1NC Class I Div 2

Manufacturer Information

Brand	Eaton
GTIN	00782114505328
Manufacturers Part Number	10250T714R
Model	Pushbutton
UPC	782114505328



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description OILTIGHT OPERATORS.30MM

Packaging

Carton 1

Weight Per each 0.4

Uses, Certifications, and Standards

Application Commercial / Institutional Buildings / Structures - Power
Distribution and Controls

standard CSA Certified,UL 508,UL 1604,CE Marked,FDA 3-A