



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



1223W Switch, Hubpro, 3-Way, 20A 120/277V, WH *Hubbell Wiring Devices*

Catalog Number	1223W
Manufacturer	Hubbell Wiring Devices
Description	Switches and Lighting Controls, Hubbell- Pro Series, Toggle Switches, General Purpose Ac, Three Way, 20A 120/277V Ac, Back and Side Wired, White
Weight per unit	0.2000 (lbs/each)
Product Category	Gen Purpose Switches

Features

action	SPDT
amperage rating	20
connection	Back and Side Wired
Contact Configuration	Two Position
Contact Rating	Per UL 20
Current Rating	20
insulation	False
operating cycles	50,000
pallet quantity	4400
Poles	1
Switch Type	Toggle
Voltage Rating	120-277
Wattage	5540;5540.0000

Material, Color, and Finish

Color	White
-------	-------

Dimensions and Weight

Size	4.18 in x 1.49 in x 1.83 in
------	-----------------------------

Descriptions

Description	SWITCH, HUBPRO, 3-WAY, 20A 120/277V, WH
extra long description	HWDK 1223W SWITCH, HUBPRO, 3-WAY, 2
Long Description	Switches and Lighting Controls, Hubbell- PRO Series, Toggle Switches, General Purpose AC, Three Way, 20A 120/277V AC, Back and Side Wired, White
Product Type	Switch, Hubpro, 3-Way, 20A 120/277V, WH
Special Features	Standard Product



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	WIRING DEVICE-KELLEMS
GTIN	00783585835334
Manufacturers Part Number	1223W
series	Heavy Duty
UPC	783585835334

Taxonomies, Classifications, and Categories

Category Description	Commercial switches
Type	TOGGLE

Packaging

Carton	1
Package	10
Weight Per each	0.2

Uses, Certifications, and Standards

Application	Back and Side Wired
Enclosure	None
environmental conditions	Indoor Dry unless protected by additional means
Mounting	Screw Mount
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
standard	UL Listed