



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 13101A6513 Ac/DC 4 Inch Perfect Prox. Cable Version *Eaton Corp*

Catalog Number	13101A6513
Manufacturer	Eaton Corp
Description	Eaton Comet 18MM Tubular Photoelectric Sensor, Perfect Prox Photoelectric Sensor, Comet, Back Ground Suppression, 4 In Range, Forward Viewing, Output On, 6.6 FT, 300 Ma Ac/DC At 20-264 Vac/15-30 VDC, PVC, Ac: L1 Switched
Weight per unit	0.6700 (lbs/each)
Product Category	Photoelectric Sensors

### Features

dimensions	2.5500 IN X 0.4700 IN X 0.7100 IN
------------	-----------------------------------

### Dimensions and Weight

Height	0.71
Length	2.55
Width	0.47

### Descriptions

Description	AC/DC 4 INCH PERFECT PROX. CABLE VERSION
extra long description	ETN 13101A6513 AC/DC 4 INCH PERFECT
Features	Eaton's Comet Series Photoelectric Sensors is a complete line of high performance, 18 mm tubular sensors with a variety of models and modes to solve virtually any sensing problem.
Long Description	Eaton Comet 18mm tubular photoelectric sensor, Perfect Prox Photoelectric Sensor, Comet, Back Ground Suppression, 4 in range, Forward Viewing, Output ON, 6.6 ft, 300 mA AC/DC at 20-264 Vac/15-30 Vdc, PVC, AC: L1 switched
Product Type	Ac/DC 4 Inch Perfect Prox. Cable Version

### Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00782113928210
Manufacturers Part Number	13101A6513
UPC	782113928210

### Taxonomies, Classifications, and Categories

Category Description	PROXIMITY SWITCHES AND CORDSETS
Type	Tubular photoelectric sensor

### Packaging

Carton	1
Weight Per each	0.67



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

Application .....	Vehicles: On-Road - PickUp & Delivery: Food .....
Operating Temperature .....	-40° to 158°F (-40° to 70°C) .....
standard .....	cUL Recognized,UL Recognized .....