




SAFETY DATA SHEET

1. Identification

| | |
|---|---|
| Product identifier | Minimal Expansion Foam |
| Other means of identification | |
| Product code | 14077 |
| Recommended use | Foam insulator and sealant |
| Recommended restrictions | None known. |
| Manufacturer/Importer/Supplier/Distributor information | |
| Manufactured or sold by: | |
| Company name | CRC Industries, Inc. |
| Address | 885 Louis Dr. Warminster, PA 18974 US |
| Telephone | |
| General Information | 215-674-4300 |
| Technical Assistance | 800-521-3168 |
| Customer Service | 800-272-4620 |
| 24-Hour Emergency (CHEMTREC) | 800-424-9300 (US) 703-527-3887 (International) |
| Website | www.crcindustries.com |

2. Hazard(s) identification

| | | |
|------------------------------|---|---|
| Physical hazards | Gases under pressure | Liquefied gas |
| Health hazards | Skin corrosion/irritation | Category 2 |
| | Serious eye damage/eye irritation | Category 2 |
| | Sensitization, respiratory | Category 1 |
| | Sensitization, skin | Category 1 |
| | Reproductive toxicity | Effects on or via lactation |
| | Specific target organ toxicity, single exposure | Category 3 respiratory tract irritation |
| | Specific target organ toxicity, repeated exposure | Category 2 |
| Environmental hazards | Hazardous to the aquatic environment, long-term hazard | Category 2 |
| OSHA defined hazards | Not classified. | |
| Label elements |  | |
| Signal word | Danger | |
| Hazard statement | Contains gas under pressure; may explode if heated. Causes skin irritation. May cause an allergic skin reaction. Causes serious eye irritation. May cause allergy or asthma symptoms or breathing difficulties if inhaled. May cause respiratory irritation. May cause harm to breast-fed children. May cause damage to organs through prolonged or repeated exposure. Toxic to aquatic life with long lasting effects. | |

Precautionary statement

Prevention

Obtain special instructions before use. Do not puncture or incinerate container. Do not expose to heat or store at temperatures above 49°C/120°F. Use with adequate ventilation. Open doors and windows or use other means to ensure a fresh air supply during use and while product is drying. If you experience any symptoms listed on this label, increase ventilation or leave the area. Do not breathe gas. Do not breathe mist or vapor. Avoid contact during pregnancy/while nursing. Do not eat, drink or smoke when using this product. Contaminated work clothing must not be allowed out of the workplace. Wear protective gloves. Wear eye/face protection. Wash thoroughly after handling. In case of inadequate ventilation wear respiratory protection. Avoid release to the environment.

Response

If on skin: Wash with plenty of water. If skin irritation or rash occurs: Get medical attention. Take off contaminated clothing and wash before reuse. If inhaled: Remove person to fresh air and keep comfortable for breathing. Call a poison center/doctor if you feel unwell. If in eyes: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. If eye irritation persists: Get medical attention. If exposed or concerned: Get medical attention. If experiencing respiratory symptoms: Call a poison center/doctor. Collect spillage.

Storage

Store locked up. Protect from sunlight. Store in a well-ventilated place. Exposure to high temperature may cause can to burst.

Disposal

Dispose of contents/container in accordance with local/regional/national regulations.

Hazard(s) not otherwise classified (HNOC)

None known.

3. Composition/information on ingredients

Mixtures

| Chemical name | Common name and synonyms | CAS number | % |
|---|--------------------------|------------|---------|
| Polypropylene polyol diphenylmethanediisocyanate prepolymer | | 9048-57-1 | 50 - 60 |
| 1,1,1,2-Tetrafluoroethane | HFC-134A | 811-97-2 | 10 - 20 |
| Alkanes, C14-17, chloro | | 85535-85-9 | 10 - 20 |
| Diphenylmethanediisocyanate, isomers and homologues | | 9016-87-9 | 5 - 10 |
| Tris(2-chloroisopropyl) phosphate | | 13674-84-5 | 5 - 10 |

Specific chemical identity and/or percentage of composition has been withheld as a trade secret.

4. First-aid measures

Inhalation

Remove victim to fresh air and keep at rest in a position comfortable for breathing. Oxygen or artificial respiration if needed. Do not use mouth-to-mouth method if victim inhaled the substance. Induce artificial respiration with the aid of a pocket mask equipped with a one-way valve or other proper respiratory medical device. If experiencing respiratory symptoms: Call a POISON CENTER or doctor/physician.

Skin contact

Remove contaminated clothing immediately and wash skin with soap and water. In case of eczema or other skin disorders: Seek medical attention and take along these instructions. Wash contaminated clothing before reuse.

Eye contact

Immediately flush eyes with plenty of water for at least 15 minutes. Remove contact lenses, if present and easy to do. Continue rinsing. Get medical attention if irritation develops and persists.

Ingestion

Rinse mouth. Drink plenty of water. Do not induce vomiting. Call a physician immediately.

Most important symptoms/effects, acute and delayed

Severe eye irritation. Symptoms may include stinging, tearing, redness, swelling, and blurred vision. May cause respiratory irritation. Difficulty in breathing. Skin irritation. May cause redness and pain. May cause an allergic skin reaction. Rash. Dermatitis. Prolonged exposure may cause chronic effects.

Indication of immediate medical attention and special treatment needed

Provide general supportive measures and treat symptomatically. Keep victim under observation. Symptoms may be delayed.

General information

IF exposed or concerned: Get medical advice/attention. Ensure that medical personnel are aware of the material(s) involved, and take precautions to protect themselves. Wash contaminated clothing before reuse.

5. Fire-fighting measures

Suitable extinguishing media Water spray. Alcohol resistant foam. Dry chemical powder. Carbon dioxide (CO₂).

| | |
|--|---|
| Unsuitable extinguishing media | Water. None known. |
| Specific hazards arising from the chemical | During fire, gases hazardous to health may be formed. |
| Special protective equipment and precautions for firefighters | Self-contained breathing apparatus and full protective clothing must be worn in case of fire. |
| Fire-fighting equipment/instructions | In case of fire: Stop leak if safe to do so. Move containers from fire area if you can do so without risk. Containers should be cooled with water to prevent vapor pressure build up. |
| General fire hazards | Contents under pressure. Pressurized container may rupture when exposed to heat or flame. |

6. Accidental release measures

| | |
|--|---|
| Personal precautions, protective equipment and emergency procedures | Keep unnecessary personnel away. Keep people away from and upwind of spill/leak. Keep out of low areas. Many gases are heavier than air and will spread along ground and collect in low or confined areas (sewers, basements, tanks). Wear appropriate protective equipment and clothing during clean-up. Do not breathe mist or vapor. Do not breathe gas. Emergency personnel need self-contained breathing equipment. Do not touch damaged containers or spilled material unless wearing appropriate protective clothing. Ventilate closed spaces before entering them. Local authorities should be advised if significant spillages cannot be contained. For personal protection, see section 8 of the SDS. |
| Methods and materials for containment and cleaning up | Keep combustibles (wood, paper, oil, etc.) away from spilled material. The product is immiscible with water and will sediment in water systems. Stop the flow of material, if this is without risk. Prevent product from entering drains. Wipe up with absorbent material (e.g. cloth, fleece). Clean surface thoroughly to remove residual contamination. For waste disposal, see section 13 of the SDS. |
| Environmental precautions | Avoid release to the environment. Prevent further leakage or spillage if safe to do so. Avoid discharge into drains, water courses or onto the ground. Inform appropriate managerial or supervisory personnel of all environmental releases. |

7. Handling and storage

| | |
|---|--|
| Precautions for safe handling | Obtain special instructions before use. Do not handle until all safety precautions have been read and understood. Pressurized container: Do not pierce or burn, even after use. Do not use if spray button is missing or defective. Do not spray on a naked flame or any other incandescent material. Do not smoke while using or until sprayed surface is thoroughly dry. Do not cut, weld, solder, drill, grind, or expose containers to heat, flame, sparks, or other sources of ignition. Use caution around energized equipment. The metal container will conduct electricity if it contacts a live source. This may result in injury to the user from electrical shock and/or flash fire. Do not breathe mist or vapor. Do not breathe gas. Avoid contact with eyes, skin, and clothing. Avoid prolonged exposure. Pregnant or breastfeeding women must not handle this product. Should be handled in closed systems, if possible. Use only in well-ventilated areas. Wear appropriate personal protective equipment. Avoid release to the environment. Observe good industrial hygiene practices. For product usage instructions, please see the product label. |
| Conditions for safe storage, including any incompatibilities | Level 1 Aerosol. Contents under pressure. Do not expose to heat or store at temperatures above 120°F/49°C as can may burst. Do not puncture, incinerate or crush. Do not handle or store near an open flame, heat or other sources of ignition. Store in a well-ventilated place. Keep out of the reach of children. Store away from incompatible materials (see Section 10 of the SDS). |

8. Exposure controls/personal protection

Occupational exposure limits

US. OSHA Table Z-1 Limits for Air Contaminants (29 CFR 1910.1000)

| Components | Type | Value |
|---|---------|-----------|
| Diphenylmethanediisocyanate, isomers and homologues (CAS 9016-87-9) | Ceiling | 0.2 mg/m3 |
| | | 0.02 ppm |

US. ACGIH Threshold Limit Values

| Components | Type | Value |
|---|------|-----------|
| Diphenylmethanediisocyanate, isomers and homologues (CAS 9016-87-9) | TWA | 0.005 ppm |

US. NIOSH: Pocket Guide to Chemical Hazards

| Components | Type | Value |
|---|---------|------------------------|
| Diphenylmethanediisocyanate, isomers and homologues (CAS 9016-87-9) | Ceiling | 0.2 mg/m ³ |
| | TWA | 0.02 ppm |
| | | 0.05 mg/m ³ |
| | | 0.005 ppm |

US. AIHA Workplace Environmental Exposure Level (WEEL) Guides

| Components | Type | Value |
|--|------|------------------------|
| 1,1,1,2-Tetrafluoroethane (CAS 811-97-2) | TWA | 4240 mg/m ³ |
| | | 1000 ppm |

| | |
|--|---|
| Biological limit values | No biological exposure limits noted for the ingredient(s). |
| Appropriate engineering controls | Good general ventilation (typically 10 air changes per hour) should be used. Ventilation rates should be matched to conditions. If applicable, use process enclosures, local exhaust ventilation, or other engineering controls to maintain airborne levels below recommended exposure limits. If exposure limits have not been established, maintain airborne levels to an acceptable level. General ventilation normally adequate. Eye wash facilities and emergency shower must be available when handling this product. |
| Individual protection measures, such as personal protective equipment | |
| Eye/face protection | Wear safety glasses with side shields (or goggles). |
| Skin protection | |
| Hand protection | Wear protective gloves such as: Rubber. Nitrile. |
| Other | Wear appropriate chemical resistant clothing. Use of an impervious apron is recommended. |
| Respiratory protection | If engineering controls are not feasible or if exposure exceeds the applicable exposure limits, use a NIOSH-approved cartridge respirator with an organic vapor cartridge. Use a self-contained breathing apparatus in confined spaces and for emergencies. Air monitoring is needed to determine actual employee exposure levels. |
| Thermal hazards | Wear appropriate thermal protective clothing, when necessary. |
| General hygiene considerations | When using, do not eat, drink or smoke. Always observe good personal hygiene measures, such as washing after handling the material and before eating, drinking, and/or smoking. Routinely wash work clothing and protective equipment to remove contaminants. Contaminated work clothing should not be allowed out of the workplace. |

9. Physical and chemical properties**Appearance**

| | |
|---|-----------------------|
| Physical state | Liquid. |
| Form | Aerosol. |
| Color | Tan. |
| Odor | Mild petroleum. |
| Odor threshold | Not available. |
| pH | Not available. |
| Melting point/freezing point | Not available. |
| Initial boiling point and boiling range | Not available. |
| Flash point | None (Tag Closed Cup) |
| Evaporation rate | Not available. |
| Flammability (solid, gas) | Not available. |
| Upper/lower flammability or explosive limits | |
| Flammability limit - lower (%) | Not available. |
| Flammability limit - upper (%) | Not available. |
| Vapor pressure | 3326.4 hPa estimated |

| | |
|--|------------------|
| Vapor density | Not available. |
| Relative density | 1.2 |
| Solubility (water) | Insoluble. |
| Partition coefficient (n-octanol/water) | Not available. |
| Auto-ignition temperature | Not available. |
| Decomposition temperature | Not available. |
| Viscosity (kinematic) | Not available. |
| Percent volatile | 22.5 % estimated |

10. Stability and reactivity

| | |
|---|---|
| Reactivity | The product is stable and non-reactive under normal conditions of use, storage and transport. |
| Chemical stability | Material is stable under normal conditions. |
| Possibility of hazardous reactions | No dangerous reaction known under conditions of normal use. |
| Conditions to avoid | Heat, flames and sparks. Contact with incompatible materials. |
| Incompatible materials | Oxidizing agents. Acids. Alcohols. |
| Hazardous decomposition products | Carbon oxides. Nitrogen oxides (NOx). Hydrogen cyanide (hydrocyanic acid). |

11. Toxicological information

Information on likely routes of exposure

| | |
|---------------------|--|
| Inhalation | May cause damage to organs through prolonged or repeated exposure by inhalation. May cause irritation to the respiratory system. May cause allergy or asthma symptoms or breathing difficulties if inhaled. Prolonged inhalation may be harmful. |
| Skin contact | Causes skin irritation. May cause an allergic skin reaction. |
| Eye contact | Causes serious eye irritation. |
| Ingestion | Health injuries are not known or expected under normal use. |

| | |
|---|--|
| Symptoms related to the physical, chemical and toxicological characteristics | Severe eye irritation. Symptoms may include stinging, tearing, redness, swelling, and blurred vision. May cause respiratory irritation. Difficulty in breathing. Skin irritation. May cause redness and pain. May cause an allergic skin reaction. Rash. Dermatitis. |
|---|--|

Information on toxicological effects

| | |
|-----------------------|--|
| Acute toxicity | May cause an allergic skin reaction. May cause respiratory irritation. |
|-----------------------|--|

| Product | Species | Test Results |
|------------------------|----------------|---|
| Minimal Expansion Foam | | |
| Acute | | |
| Dermal | | |
| LD50 | Rat | 66667 mg/kg estimated |
| Inhalation | | |
| LC50 | Rat | 4920 mg/m3, 4 hours estimated 4.6 mg/l estimated |
| Oral | | |
| LD50 | Rat | 15556 mg/kg estimated |

* Estimates for product may be based on additional component data not shown.

| | |
|--|--|
| Skin corrosion/irritation | Causes skin irritation. |
| Serious eye damage/eye irritation | Causes serious eye irritation. |
| Respiratory sensitization | May cause allergy or asthma symptoms or breathing difficulties if inhaled. |
| Skin sensitization | May cause an allergic skin reaction. |
| Germ cell mutagenicity | No data available to indicate product or any components present at greater than 0.1% are mutagenic or genotoxic. |
| Carcinogenicity | This product is not considered to be a carcinogen by IARC, ACGIH, NTP, or OSHA. |

IARC Monographs. Overall Evaluation of Carcinogenicity

Diphenylmethanediisocyanate, isomers and homologues 3 Not classifiable as to carcinogenicity to humans.
(CAS 9016-87-9)

US. National Toxicology Program (NTP) Report on Carcinogens

Not available.

| | |
|---|---|
| Reproductive toxicity | May cause harm to breastfed babies. |
| Specific target organ toxicity - single exposure | May cause respiratory irritation. |
| Specific target organ toxicity - repeated exposure | May cause damage to organs through prolonged or repeated exposure. |
| Aspiration hazard | Not likely, due to the form of the product. |
| Chronic effects | Prolonged inhalation may be harmful. May cause damage to organs through prolonged or repeated exposure. |

12. Ecological information

| | |
|--|---|
| Ecotoxicity | Toxic to aquatic life with long lasting effects. |
| Persistence and degradability | No data is available on the degradability of this product. |
| Bioaccumulative potential | No data available. |
| Partition coefficient n-octanol / water (log Kow) | |
| 1,1,1,2-Tetrafluoroethane | 1.274 |
| Mobility in soil | No data available. |
| Other adverse effects | No other adverse environmental effects (e.g. ozone depletion, photochemical ozone creation potential, endocrine disruption, global warming potential) are expected from this component. |

13. Disposal considerations

| | |
|--|--|
| Disposal of waste from residues / unused products | This product is not a RCRA hazardous waste (See 40 CFR Part 261.20 – 261.33). Empty containers may be recycled. Collect and reclaim or dispose in sealed containers at licensed waste disposal site. Contents under pressure. Do not puncture, incinerate or crush. Do not allow this material to drain into sewers/water supplies. Do not contaminate ponds, waterways or ditches with chemical or used container. Dispose in accordance with all applicable regulations. |
| Hazardous waste code | Not regulated. |
| Contaminated packaging | Empty containers should be taken to an approved waste handling site for recycling or disposal. Since emptied containers may retain product residue, follow label warnings even after container is emptied. |

14. Transport information

DOT

| | |
|-------------------------------------|---|
| UN number | UN1950 |
| UN proper shipping name | Aerosols, non-flammable, Limited Quantity |
| Transport hazard class(es) | |
| Class | 2.2 |
| Subsidiary risk | - |
| Label(s) | 2.2 |
| Packing group | Not applicable. |
| Special precautions for user | Read safety instructions, SDS and emergency procedures before handling. |
| Special provisions | Not available. |
| Packaging exceptions | 306 |
| Packaging non bulk | None |
| Packaging bulk | None |

IATA

| | |
|-------------------------------------|---|
| UN number | UN1950 |
| UN proper shipping name | Aerosols, non-flammable |
| Transport hazard class(es) | |
| Class | 2.2 |
| Subsidiary risk | - |
| Packing group | Not applicable. |
| Environmental hazards | No. |
| ERG Code | 2L |
| Special precautions for user | Read safety instructions, SDS and emergency procedures before handling. |

Other information

Passenger and cargo aircraft Allowed.
Cargo aircraft only Allowed.

IMDG

UN number UN1950
UN proper shipping name AEROSOLS, LIMITED QUANTITY
Transport hazard class(es)
Class 2
Subsidiary risk -
Packing group Not applicable.
Environmental hazards
Marine pollutant No.
EmS F-D, S-U
Special precautions for user Read safety instructions, SDS and emergency procedures before handling.

15. Regulatory information

US federal regulations This product is a "Hazardous Chemical" as defined by the OSHA Hazard Communication Standard, 29 CFR 1910.1200.
All components are on the U.S. EPA TSCA Inventory List.

TSCA Section 12(b) Export Notification (40 CFR 707, Subpt. D)

Not regulated.

TSCA Chemical Action Plans, Chemicals of Concern

Alkanes, C14-17, chloro (CAS 85535-85-9) Short-Chain Chlorinated Paraffins (SCCPs) and Other Chlorinated Paraffins Action Plan
Diphenylmethanediisocyanate, isomers and homologues (CAS 9016-87-9) Methylene Diphenyl Diisocyanate (MDI) And Related Compounds Action Plan [RIN 2070-ZA15]

US. OSHA Specifically Regulated Substances (29 CFR 1910.1001-1050)

Not listed.

SARA 304 Emergency release notification

Not regulated.

US EPCRA (SARA Title III) Section 313 - Toxic Chemical: Listed substance

Diphenylmethanediisocyanate, isomers and homologues (CAS 9016-87-9)

CERCLA Hazardous Substance List (40 CFR 302.4)

Diphenylmethanediisocyanate, isomers and homologues (CAS 9016-87-9) Listed.

CERCLA Hazardous Substances: Reportable quantity

Diphenylmethanediisocyanate, isomers and homologues (CAS 9016-87-9) 5000 LBS

Spills or releases resulting in the loss of any ingredient at or above its RQ require immediate notification to the National Response Center (800-424-8802) and to your Local Emergency Planning Committee.

Clean Air Act (CAA) Section 112 Hazardous Air Pollutants (HAPs) List

Diphenylmethanediisocyanate, isomers and homologues (CAS 9016-87-9)

Clean Air Act (CAA) Section 112(r) Accidental Release Prevention (40 CFR 68.130)

Not regulated.

Safe Drinking Water Act (SDWA) Not regulated.

Food and Drug Administration (FDA) Not regulated.

Superfund Amendments and Reauthorization Act of 1986 (SARA)

Section 311/312
Hazard categories Immediate Hazard - Yes
Delayed Hazard - Yes
Fire Hazard - No
Pressure Hazard - Yes
Reactivity Hazard - No

SARA 302 Extremely hazardous substance No

US state regulations

US. California. Candidate Chemicals List. Safer Consumer Products Regulations (Cal. Code Regs, tit. 22, 69502.3, subd. (a))

Tris(2-chloroisopropyl) phosphate (CAS 13674-84-5)
Alkanes, C14-17, chloro (CAS 85535-85-9)
Diphenylmethanediisocyanate, isomers and homologues (CAS 9016-87-9)

US. California Controlled Substances. CA Department of Justice (California Health and Safety Code Section 11100)

Not listed.

US. New Jersey Worker and Community Right-to-Know Act

Diphenylmethanediisocyanate, isomers and homologues (CAS 9016-87-9)

US. Massachusetts RTK - Substance List

Diphenylmethanediisocyanate, isomers and homologues (CAS 9016-87-9)

US. Pennsylvania Worker and Community Right-to-Know Law

Diphenylmethanediisocyanate, isomers and homologues (CAS 9016-87-9)

US. Rhode Island RTK

Diphenylmethanediisocyanate, isomers and homologues (CAS 9016-87-9)

US. California Proposition 65

California Safe Drinking Water and Toxic Enforcement Act of 1986 (Proposition 65): This material is not known to contain any chemicals currently listed as carcinogens or reproductive toxins.

Volatile organic compounds (VOC) regulations

EPA

VOC content (40 CFR 51.100(s)) 2.9 %

Consumer products (40 CFR 59, Subpt. C) Not regulated

State

Consumer products Not regulated

VOC content (CA) 2.9 %

VOC content (OTC) 2.9 %

International Inventories

| Country(s) or region | Inventory name | On inventory (yes/no)* |
|-----------------------------|--|------------------------|
| Australia | Australian Inventory of Chemical Substances (AICS) | Yes |
| Canada | Domestic Substances List (DSL) | Yes |
| Canada | Non-Domestic Substances List (NDSL) | No |
| China | Inventory of Existing Chemical Substances in China (IECSC) | Yes |
| Europe | European Inventory of Existing Commercial Chemical Substances (EINECS) | No |
| Europe | European List of Notified Chemical Substances (ELINCS) | No |
| Japan | Inventory of Existing and New Chemical Substances (ENCS) | No |
| Korea | Existing Chemicals List (ECL) | Yes |
| New Zealand | New Zealand Inventory | Yes |
| Philippines | Philippine Inventory of Chemicals and Chemical Substances (PICCS) | Yes |
| United States & Puerto Rico | Toxic Substances Control Act (TSCA) Inventory | Yes |

*A "Yes" indicates that all components of this product comply with the inventory requirements administered by the governing country(s)

A "No" indicates that one or more components of the product are not listed or exempt from listing on the inventory administered by the governing country(s).

16. Other information, including date of preparation or last revision

| | |
|---------------------|----------------|
| Issue date | 02-13-2015 |
| Revision date | 08-28-2015 |
| Prepared by | Allison Cho |
| Version # | 02 |
| Further information | Not available. |

HMIS® ratings

Health: 2*
Flammability: 1
Physical hazard: 1
Personal protection: B

NFPA ratings

Health: 2
Flammability: 1
Instability: 1

NFPA ratings



Disclaimer

The information contained in this document applies to this specific material as supplied. It may not be valid for this material if it is used in combination with any other materials. This information is accurate to the best of CRC Industries' knowledge or obtained from sources believed by CRC to be accurate. Before using any product, read all warnings and directions on the label. For further clarification of any information contained on this (M)SDS consult your supervisor, a health & safety professional, or CRC Industries.