



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 14100AQD03 Ac/DC Ir Reflex With Micro Connector *Eaton Corp*

Catalog Number	14100AQD03
Manufacturer	Eaton Corp
Description	Eaton Comet Series Tubular Photoelectric Sensor, Forward Viewing, Sensor Dist 25 FT., 300 Ma Max Ac L1 Switched/DC NPN Open Coll, 300 Ma Ac/DC At 20-264VAC/15-30VDC, 4 Pin Dual Key Micro Connector, Non Polarized Retroreflective, 8 In(.2M)
Weight per unit	0.7000 (lbs/each)
Product Category	Photoelectric Sensors

### Features

connection	4-pin dual key micro connector
------------	--------------------------------

### Dimensions and Weight

Height	1.8
Length	0.47
Width	0.71

### Descriptions

Description	AC/DC IR REFLEX WITH MICRO CONNECTOR
extra long description	ETN 14100AQD03 AC/DC IR REFLEX WITH
Features	Eaton's Comet Series Photoelectric Sensors is a complete line of high performance, 18 mm tubular sensors with a variety of models and modes to solve virtually any sensing problem.
Long Description	Eaton Comet Series Tubular Photoelectric Sensor, Forward Viewing, Sensor dist 25 Ft., 300 mA max AC L1 switched/DC NPN open coll, 300 mA AC/DC at 20-264Vac/15-30Vdc, 4 Pin Dual Key Micro Connector, Non Polarized Retroreflective, 8 in(.2m)
Product Type	Ac/DC Ir Reflex With Micro Connector

### Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00782113843667
Manufacturers Part Number	14100AQD03
UPC	782113843667

### Taxonomies, Classifications, and Categories

Category Description	PROXIMITY SWITCHES AND CORDSETS
Type	Tubular photoelectric sensor

### Packaging

Carton	1
Weight Per each	0.7



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

Application

Elec Assemblies, Panels & OEM - Electrical Assemblies and  
OEMs - Other

Operating Temperature

-40° to 158°F (-40° to 70°C)

standard

cUL Recognized,UL Recognized,CE Marked