



SAFETY DATA SHEET

1. Identification

Product identifier	HydroForce® Super Citrus™ Heavy Duty Degreaser - 15 oz
Other means of identification	
Product Code	No. 14440 (Item# 1004984)
Recommended use	General purpose degreaser
Recommended restrictions	None known.
Manufacturer/Importer/Supplier/Distributor information	
Manufactured or sold by:	
Company name	CRC Industries, Inc.
Address	885 Louis Dr. Warminster, PA 18974 US
Telephone	
General Information	215-674-4300
Technical Assistance	800-521-3168
Customer Service	800-272-4620
24-Hour Emergency (CHEMTREC)	800-424-9300 (US)
Website	www.crcindustries.com

2. Hazard(s) identification

Physical hazards	Gases under pressure	Liquefied gas
Health hazards	Skin corrosion/irritation	Category 2
	Serious eye damage/eye irritation	Category 2A
	Sensitization, skin	Category 1
Environmental hazards	Hazardous to the aquatic environment, acute hazard	Category 2
	Hazardous to the aquatic environment, long-term hazard	Category 2
OSHA defined hazards	Not classified.	
Label elements		



Signal word	Warning
Hazard statement	Contains gas under pressure; may explode if heated. Causes skin irritation. May cause an allergic skin reaction. Causes serious eye irritation. Toxic to aquatic life. Toxic to aquatic life with long lasting effects.
Precautionary statement	
Prevention	Do not puncture or incinerate container. Do not expose to heat or store at temperatures above 49 °C/120 °F. Use with adequate ventilation. Open doors and windows or use other means to ensure a fresh air supply during use and while product is drying. If you experience any symptoms listed on this label, increase ventilation or leave the area. Avoid breathing vapors. Wash thoroughly after handling. Contaminated work clothing must not be allowed out of the workplace. Wear eye protection/face protection. Wear protective gloves. Avoid release to the environment.
Response	If on skin: Wash with plenty of water. If skin irritation or rash occurs: Get medical advice/attention. Take off contaminated clothing and wash before reuse. If in eyes: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. If eye irritation persists: Get medical advice/attention. Collect spillage.

Storage	Protect from sunlight. Store in a well-ventilated place. Exposure to high temperature may cause can to burst.
Disposal	Dispose of contents/container in accordance with local/regional/national regulations.
Hazard(s) not otherwise classified (HNOC)	None known.
Supplemental information	None.

3. Composition/information on ingredients

Mixtures

Chemical name	Common name and synonyms	CAS number	%
water		7732-18-5	60 - 70
1,1-difluoroethane	HFC-152a	75-37-6	10 - 20
d-limonene		5989-27-5	5 - 10
soybean oil, methyl ester		67784-80-9	5 - 10
tallow alkyl amines, ethoxylated		61791-26-2	1 - 3

Specific chemical identity and/or percentage of composition has been withheld as a trade secret.

4. First-aid measures

Inhalation	Move to fresh air. Call a physician if symptoms develop or persist.
Skin contact	Remove contaminated clothing immediately and wash skin with soap and water. In case of eczema or other skin disorders: Seek medical attention and take along these instructions. Wash contaminated clothing before reuse.
Eye contact	Immediately flush eyes with plenty of water for at least 15 minutes. Remove contact lenses, if present and easy to do. Continue rinsing. Get medical attention if irritation develops and persists.
Ingestion	In the unlikely event of swallowing contact a physician or poison control center. Rinse mouth.
Most important symptoms/effects, acute and delayed	Severe eye irritation. Symptoms may include stinging, tearing, redness, swelling, and blurred vision. Skin irritation. May cause redness and pain. May cause an allergic skin reaction. Dermatitis. Rash.
Indication of immediate medical attention and special treatment needed	Provide general supportive measures and treat symptomatically. Keep victim under observation. Symptoms may be delayed.
General information	Ensure that medical personnel are aware of the material(s) involved, and take precautions to protect themselves. Wash contaminated clothing before reuse.

5. Fire-fighting measures

Suitable extinguishing media	Water fog. Foam. Dry chemical powder. Carbon dioxide (CO ₂).
Unsuitable extinguishing media	Do not use water jet as an extinguisher, as this will spread the fire.
Specific hazards arising from the chemical	Pressurized container may rupture when exposed to heat or flame. During fire, gases hazardous to health may be formed.
Special protective equipment and precautions for firefighters	Self-contained breathing apparatus and full protective clothing must be worn in case of fire.
Fire-fighting equipment/instructions	In case of fire: Stop leak if safe to do so. Move containers from fire area if you can do so without risk. Containers should be cooled with water to prevent vapor pressure build up.
General fire hazards	Contents under pressure. Pressurized container may rupture when exposed to heat or flame.

6. Accidental release measures

Personal precautions, protective equipment and emergency procedures	Keep unnecessary personnel away. Keep people away from and upwind of spill/leak. Keep out of low areas. Many gases are heavier than air and will spread along ground and collect in low or confined areas (sewers, basements, tanks). Wear appropriate protective equipment and clothing during clean-up. Avoid breathing mist or vapor. Emergency personnel need self-contained breathing equipment. Do not touch damaged containers or spilled material unless wearing appropriate protective clothing. Ventilate closed spaces before entering them. Local authorities should be advised if significant spillages cannot be contained. For personal protection, see section 8 of the SDS.
--	--

Methods and materials for containment and cleaning up

Eliminate all ignition sources (no smoking, flares, sparks, or flames in immediate area). Keep combustibles (wood, paper, oil, etc.) away from spilled material. This product is miscible in water. This material is classified as a water pollutant under the Clean Water Act and should be prevented from contaminating soil or from entering sewage and drainage systems which lead to waterways. Stop the flow of material, if this is without risk. Wipe up with absorbent material (e.g. cloth, fleece). Clean surface thoroughly to remove residual contamination. For waste disposal, see section 13 of the SDS.

Environmental precautions

Avoid release to the environment. Inform appropriate managerial or supervisory personnel of all environmental releases. Prevent further leakage or spillage if safe to do so. Avoid discharge into drains, water courses or onto the ground.

7. Handling and storage

Precautions for safe handling

Pressurized container: Do not pierce or burn, even after use. Do not use if spray button is missing or defective. Do not spray on a naked flame or any other incandescent material. Do not smoke while using or until sprayed surface is thoroughly dry. Do not cut, weld, solder, drill, grind, or expose containers to heat, flame, sparks, or other sources of ignition. Use caution around energized equipment. The metal container will conduct electricity if it contacts a live source. This may result in injury to the user from electrical shock and/or flash fire. Avoid breathing mist or vapor. Avoid contact with eyes, skin, and clothing. Avoid prolonged exposure. Use only in well-ventilated areas. Wear appropriate personal protective equipment. Avoid release to the environment. Observe good industrial hygiene practices. For product usage instructions, see the product label.

Conditions for safe storage, including any incompatibilities

Level 1 Aerosol.

Contents under pressure. Do not expose to heat or store at temperatures above 120°F/49°C as can may burst. Do not puncture, incinerate or crush. Do not handle or store near an open flame, heat or other sources of ignition. Store in a well-ventilated place. Stored containers should be periodically checked for general condition and leakage. Store away from incompatible materials (see Section 10 of the SDS).

8. Exposure controls/personal protection

Occupational exposure limits

US. Workplace Environmental Exposure Level (WEEL) Guides

Components	Type	Value
1,1-difluoroethane (CAS 75-37-6)	TWA	2700 mg/m3
		1000 ppm
d-limonene (CAS 5989-27-5)	TWA	165.5 mg/m3
		30 ppm

Biological limit values

No biological exposure limits noted for the ingredient(s).

Appropriate engineering controls

Good general ventilation (typically 10 air changes per hour) should be used. Ventilation rates should be matched to conditions. If applicable, use process enclosures, local exhaust ventilation, or other engineering controls to maintain airborne levels below recommended exposure limits. If exposure limits have not been established, maintain airborne levels to an acceptable level. Eye wash facilities and emergency shower should be available when handling this product.

Individual protection measures, such as personal protective equipment

Eye/face protection

Wear safety glasses with side shields (or goggles).

Skin protection

Hand protection

Wear protective gloves such as: Rubber. Nitrile.

Other

Wear appropriate chemical resistant clothing.

Respiratory protection

If engineering controls are not feasible or if exposure exceeds the applicable exposure limits, use a NIOSH-approved cartridge respirator with an organic vapor cartridge. Use a self-contained breathing apparatus in confined spaces and for emergencies. Air monitoring is needed to determine actual employee exposure levels.

Thermal hazards

Wear appropriate thermal protective clothing, when necessary.

General hygiene considerations

When using do not smoke. Always observe good personal hygiene measures, such as washing after handling the material and before eating, drinking, and/or smoking. Routinely wash work clothing and protective equipment to remove contaminants. Contaminated work clothing should not be allowed out of the workplace.

9. Physical and chemical properties

Appearance

Physical state	Liquid.
Form	Aerosol.
Color	Creamy white.

Odor Citrus.

Odor threshold Not available.

pH 10

Melting point/freezing point -140.8 °F (-96 °C) estimated

Initial boiling point and boiling range 212 °F (100 °C) estimated

Flash point None.

Evaporation rate Slow.

Flammability (solid, gas) Not available.

Upper/lower flammability or explosive limits

Flammability limit - lower (%) 0.7 % estimated

Flammability limit - upper (%) 23.5 % estimated

Vapor pressure 1230.1 hPa estimated

Vapor density > 1 (air = 1)

Relative density 0.96

Solubility(ies)

Solubility (water) Soluble.

Partition coefficient (n-octanol/water) Not available.

Auto-ignition temperature 302 °F (150 °C) estimated

Decomposition temperature Not available.

Viscosity Not available.

Percent volatile 95.7 % estimated

10. Stability and reactivity

Reactivity The product is stable and non-reactive under normal conditions of use, storage and transport.

Chemical stability Material is stable under normal conditions.

Possibility of hazardous reactions No dangerous reaction known under conditions of normal use.

Conditions to avoid Heat, flames and sparks. Contact with incompatible materials.

Incompatible materials Strong oxidizing agents.

Hazardous decomposition products Oxides of d-limonene. Carbon oxides.

11. Toxicological information

Information on likely routes of exposure

Inhalation Prolonged inhalation may be harmful.

Skin contact Causes skin irritation. May cause an allergic skin reaction.

Eye contact Causes serious eye irritation.

Ingestion Expected to be a low ingestion hazard.

Symptoms related to the physical, chemical and toxicological characteristics Severe eye irritation. Symptoms may include stinging, tearing, redness, swelling, and blurred vision. Skin irritation. May cause redness and pain. May cause an allergic skin reaction. Dermatitis. Rash.

Information on toxicological effects

Acute toxicity Not known.

Components	Species	Test Results
d-limonene (CAS 5989-27-5)		
Acute		
Dermal		
LD50	Rabbit	5 g/kg
Oral		
LD50	Rat	4400 mg/kg
soybean oil, methyl ester (CAS 67784-80-9)		
Acute		
Dermal		
LD50	Rabbit	2000 - 20000 mg/kg
Oral		
LD50	Rat	5000 - 15000 mg/kg
tallow alkyl amines, ethoxylated (CAS 61791-26-2)		
Acute		
Dermal		
LD50	Rabbit	> 10000 mg/kg
Skin corrosion/irritation	Causes skin irritation.	
Serious eye damage/eye irritation	Causes serious eye irritation.	
Respiratory or skin sensitization		
Respiratory sensitization	Not a respiratory sensitizer.	
Skin sensitization	May cause an allergic skin reaction.	
Germ cell mutagenicity	No data available to indicate product or any components present at greater than 0.1% are mutagenic or genotoxic.	
Carcinogenicity	Not classifiable as to carcinogenicity to humans.	
IARC Monographs. Overall Evaluation of Carcinogenicity		
d-limonene (CAS 5989-27-5)	3 Not classifiable as to carcinogenicity to humans.	
OSHA Specifically Regulated Substances (29 CFR 1910.1001-1052)		
Not regulated.		
US. National Toxicology Program (NTP) Report on Carcinogens		
Not listed.		
Reproductive toxicity	This product is not expected to cause reproductive or developmental effects.	
Specific target organ toxicity - single exposure	Not classified.	
Specific target organ toxicity - repeated exposure	Not classified.	
Aspiration hazard	Not an aspiration hazard.	
Chronic effects	Prolonged inhalation may be harmful.	

12. Ecological information

Ecotoxicity Toxic to aquatic life with long lasting effects.

Components	Species	Test Results
d-limonene (CAS 5989-27-5)		
Aquatic		
Fish	LC50	Fathead minnow (Pimephales promelas) 0.619 - 0.796 mg/l, 96 hours
<i>Acute</i>		
Crustacea	EC50	Water flea (Daphnia magna) 0.421 mg/l, 48 hours
Fish	LC50	Fathead minnow (Pimephales promelas) 0.619 - 0.796 mg/l, 96 hours

Components	Species	Test Results
soybean oil, methyl ester (CAS 67784-80-9)		
Aquatic		
<i>Acute</i>		
Crustacea	EC50	Crustacea 800 - 5243 mg/l, 48 hours
Fish	LC50	Fish > 1000 mg/l, 96 hours
tallow alkyl amines, ethoxylated (CAS 61791-26-2)		
Aquatic		
Fish	LC50	Fathead minnow (<i>Pimephales promelas</i>) 1 mg/l, 96 hours
<i>Acute</i>		
Algae	IC50	Algae 0.1 - 1 mg/l, 72 hours
Crustacea	EC50	Water flea (<i>Daphnia magna</i>) 0.17 mg/l, 48 hours
Fish	LC50	Rainbow trout, donaldson trout (<i>Oncorhynchus mykiss</i>) 0.13 mg/l, 96 hours
Persistence and degradability	No data is available on the degradability of any ingredients in the mixture.	
Bioaccumulative potential		
Partition coefficient n-octanol / water (log Kow)		
1,1-difluoroethane		0.75
d-limonene		4.232
Mobility in soil	No data available.	
Other adverse effects	No other adverse environmental effects (e.g. ozone depletion, photochemical ozone creation potential, endocrine disruption, global warming potential) are expected from this component.	

13. Disposal considerations

Disposal instructions	The dispensed liquid product is not a RCRA hazardous waste (See 40 CFR Part 261.20 - 261.33). Empty container can be recycled. Collect and reclaim or dispose in sealed containers at licensed waste disposal site. Contents under pressure. Do not puncture, incinerate or crush. Do not allow this material to drain into sewers/water supplies. Do not contaminate ponds, waterways or ditches with chemical or used container. Dispose in accordance with all applicable regulations.
Hazardous waste code	Not regulated.
Contaminated packaging	Empty containers should be taken to an approved waste handling site for recycling or disposal. Since emptied containers may retain product residue, follow label warnings even after container is emptied.

14. Transport information

DOT

UN number	UN1950
UN proper shipping name	Aerosols, non-flammable, Limited Quantity
Transport hazard class(es)	
Class	2.2
Subsidiary risk	-
Label(s)	2.2
Packing group	Not applicable.
Special precautions for user	Read safety instructions, SDS and emergency procedures before handling.
Packaging exceptions	306
Packaging non bulk	None
Packaging bulk	None

IATA


UN number	UN1950
UN proper shipping name	Aerosols, non-flammable, Limited Quantity
Transport hazard class(es)	
Class	2.2
Subsidiary risk	-
Packing group	Not applicable.
ERG Code	2L
Special precautions for user	Read safety instructions, SDS and emergency procedures before handling.

Other information

Passenger and cargo aircraft Allowed with restrictions.
Cargo aircraft only Allowed with restrictions.

IMDG

UN number UN1950
UN proper shipping name AEROSOLS, Limited Quantity
Transport hazard class(es)
Class 2.2
Subsidiary risk -
Packing group Not applicable.
Environmental hazards
Marine pollutant Yes, but exempt from the regulations.
EmS Not available.
Special precautions for user Read safety instructions, SDS and emergency procedures before handling.

DOT; IMDG**IATA**

15. Regulatory information

US federal regulations This product is a "Hazardous Chemical" as defined by the OSHA Hazard Communication Standard, 29 CFR 1910.1200.
All components are on the U.S. EPA TSCA Inventory List.

TSCA Section 12(b) Export Notification (40 CFR 707, Subpt. D)

Not regulated.

SARA 304 Emergency release notification

Not regulated.

OSHA Specifically Regulated Substances (29 CFR 1910.1001-1052)

Not regulated.

CERCLA Hazardous Substance List (40 CFR 302.4)

Not listed.

CERCLA Hazardous Substances: Reportable quantity

Not listed.

Spills or releases resulting in the loss of any ingredient at or above its RQ require immediate notification to the National Response Center (800-424-8802) and to your Local Emergency Planning Committee.

Other federal regulations**Clean Air Act (CAA) Section 112 Hazardous Air Pollutants (HAPs) List**

Not regulated.

Clean Air Act (CAA) Section 112(r) Accidental Release Prevention (40 CFR 68.130)

1,1-difluoroethane (CAS 75-37-6)

Safe Drinking Water Act (SDWA) Not regulated.**Food and Drug Administration (FDA)** Not regulated.**Superfund Amendments and Reauthorization Act of 1986 (SARA)****Classified hazard categories** Gas under pressure
Skin corrosion or irritation
Serious eye damage or eye irritation
Respiratory or skin sensitization**SARA 302 Extremely hazardous substance**

Not listed.

SARA 311/312 Hazardous chemical Yes**SARA 313 (TRI reporting)**
Not regulated.**US state regulations****US. New Jersey Worker and Community Right-to-Know Act**

1,1-difluoroethane (CAS 75-37-6)

US. Massachusetts RTK - Substance List

1,1-difluoroethane (CAS 75-37-6)

US. Pennsylvania Worker and Community Right-to-Know Law

Not listed.

US. Rhode Island RTK

Not listed.

California Proposition 65**WARNING:** Cancer and Reproductive Harm - www.P65Warnings.ca.gov**California Proposition 65 - CRT: Listed date/Carcinogenic substance**

beta-myrcene (CAS 123-35-3)

Listed: March 27, 2015

diethanolamine (CAS 111-42-2)

Listed: June 22, 2012

California Proposition 65 - CRT: Listed date/Developmental toxin

methanol (CAS 67-56-1)

Listed: March 16, 2012

Volatile organic compounds (VOC) regulations**EPA****VOC content (40 CFR 51.100(s))** 19.6 %**Consumer products (40 CFR 59, Subpt. C)** Not regulated**State****Consumer products** This product is regulated as a General Purpose Degreaser (aerosol). This product is compliant for use in all 50 states.**VOC content (CA)** 9.8 %**VOC content (OTC)** 9.8 %**International Inventories**

Country(s) or region	Inventory name	On inventory (yes/no)*
Australia	Australian Inventory of Chemical Substances (AICS)	No
Canada	Domestic Substances List (DSL)	Yes
Canada	Non-Domestic Substances List (NDSL)	No
China	Inventory of Existing Chemical Substances in China (IECSC)	No
Europe	European Inventory of Existing Commercial Chemical Substances (EINECS)	No
Europe	European List of Notified Chemical Substances (ELINCS)	No

Country(s) or region	Inventory name	On inventory (yes/no)*
Japan	Inventory of Existing and New Chemical Substances (ENCS)	No
Korea	Existing Chemicals List (ECL)	No
New Zealand	New Zealand Inventory	No
Philippines	Philippine Inventory of Chemicals and Chemical Substances (PICCS)	No
Taiwan	Taiwan Chemical Substance Inventory (TCSI)	No
United States & Puerto Rico	Toxic Substances Control Act (TSCA) Inventory	Yes

*A "Yes" indicates that all components of this product comply with the inventory requirements administered by the governing country(s)
A "No" indicates that one or more components of the product are not listed or exempt from listing on the inventory administered by the governing country(s).

16. Other information, including date of preparation or last revision

Issue date	03-28-2019
Prepared by	Dustin Kern
Version #	01
Further information	CRC # 667C/1002699
Disclaimer	The information contained in this document applies to this specific material as supplied. It may not be valid for this material if it is used in combination with any other materials. This information is accurate to the best of CRC's knowledge or obtained from sources believed by CRC to be accurate. Before using any product, read all warnings and directions on the label. For further clarification of any information contained on this (M)SDS consult your supervisor, a health & safety professional, or CRC Industries, Inc..
Revision information	Product and Company Identification: Product and Company Identification Hazard(s) identification: Prevention Hazard(s) identification: Supplemental information First-aid measures: Ingestion Fire-fighting measures: Unsuitable extinguishing media Fire-fighting measures: Specific hazards arising from the chemical Handling and storage: Precautions for safe handling Stability and reactivity: Conditions to avoid Stability and reactivity: Hazardous decomposition products Transport Information: Material Transportation Information Regulatory information: Consumer products GHS: Classification