



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



1411D6501 Reflex, Self-Contained, 115VAC, 11-Series, Plug-In Rel *Eaton Corp*

Catalog Number	1411D6501
Manufacturer	Eaton Corp
Description	Eaton E68 Series Integral Sensor Valve Zero Pressure Accumulation Sensor, Photoelectric, Right Angle, Structural Polyurethane Foam Enclosure, 4 Pin M12 Connector, 18 - 30 VDC Input, Polarized Retroreflective
Weight per unit	1.3 (lbs/each)
Product Category	Photoelectric Sensors

Features

dimensions	3.7900 IN X 7.6500 IN X 5.7000 IN
------------	-----------------------------------

Dimensions and Weight

Height	5.7
Length	3.79
Width	7.65

Descriptions

Description	REFLEX,SELF-CONTAINED,115VAC,11-SERIES,PLUG-IN REL
extra long description	ETN 1411D-6501 PHOTO SENSOR,REFLEX,
Features	The 11 series are highly configurable photoelectric sensor. The sensor operates in the reflex sensing mode with a choice of visible or infrared source light. Select one of four different output devices to match your control needs. An optional time delay logic module is also available.
Long Description	Eaton E68 Series Integral Sensor Valve Zero Pressure Accumulation Sensor, Photoelectric, Right Angle, Structural Polyurethane Foam enclosure, 4 Pin M12 Connector, 18 - 30 Vdc input, Polarized Retroreflective
Product Type	Photo Sensor, Reflex, 115vac

Manufacturer Information

Brand	Eaton
GTIN	00782113824574
Manufacturers Part Number	1411D6501
UPC	782113824574

Taxonomies, Classifications, and Categories

Category Description	PROXIMITY SWITCHES AND CORDSETS
Type	Photoelectric Sensor

Packaging

Carton	1
Weight Per each	1.2999



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application	Stationary Mach Equip In Factory - Other Stationary Machinery and Equipment - In Factory
Operating Temperature	5° to 131°F (-15° to 55°C)
standard	Contact Manufacturer