



Pass & Seymour

Switches TradeMaster® Decorator Combination Switches




Unique “Up/Down” switches match the look and feel of standard Decorator switches.

Easy-to-use oversized main switch for primary load.

Patented Snap-In Light Module (sold separately) transforms a combination switch into an illuminated switch in seconds.

Identification modules (sold separately) identifies each switch — light, fan, heat lamp.



TM8113WCC
Shown with Snap-In Light Module TM8LMCC.

Fully rounded back body protects wires from being damaged by sharp edges.

Ground screw position under the end of the strap minimizes the risk of contact.

Impact-resistant face and body.

Full wraparound metal strap, commercial grade with lock-in tabs.




All screws are tri-drive.

Patented split circuit tab — easily accessible, and can be reinstalled without a tool.

External screw-pressure-plate back and side wired. Accepts #12 and #14 AWG.

Adding a Snap-In Light Module



Features

- Module simply snaps-in for easy installation.
 - Can be installed with the following devices: TM811, TM813, TM833, TM818, TM838, TM8111, TM8113, TM81111, TM8118 and the LS Series of Dimmers & Fan Speed Controls (see Pages M-13 through M-15).
- Snap-In Light Module:**
- Lights when OFF.
 - Uses energy-efficient 1/4 watt LED light.
 - LED light will not generate heat and will last on average 47 years.



Catalog Number	Rating		Color	3rd Party Compliance
	A.	VAC		cULus cULus
Snap-In Light Module				
TM8LMCC	15	120/125	Clear	•
Identification Modules				
TM81DICC	—	—	Ivory	
TM81DWCC	—	—	White	
TM81DCC	—	—	Brown	
TM81DBKCC	—	—	Black	
TM81DLACC	—	—	Light Almond	

For Decorator Hallway Lights and Combination Devices, see Page D-24.

All devices listed on this page conform to NEMA WD-1 and WD-6.


Switches Decorator Combination Tamper-Resistant Switch/GFCI Receptacles

15A, 125VAC



Pass & Seymour

Features	
<ul style="list-style-type: none"> Protects children: patented shutter system helps prevent improper insertion of foreign objects. Meets National Electrical Code® Tamper-Resistant requirements. SafeLock™ Protection: if critical components are damaged and ground fault protection is lost, power to receptacle is disconnected. Up-down switching. 15 Amp single pole switch rated for 1/2 HP motor loads – perfect for bath or kitchen vents and garbage disposals. Prevents line-load reversal miswire: no power to the face or downstream receptacles if wired incorrectly. Exceeds UL943 voltage surge requirements; survives 100x the required UL 3kA/6kV voltage surge test cycles. Trip indicator light (red LED). Two back wire holes per terminal. 	<ul style="list-style-type: none"> Side or internal screw-pressure-plate back wire with #10 – #14 AWG solid or stranded copper wire. Ground screw has a back wire clamp for easy installation. 1/4" thinner than competitors' GFCIs; leaves more room for wires in the box. Mounting screws are shipped captive in the device and wall plate for easier installation. High-impact-resistant thermoplastic construction. Extra-long strap. Button colors match the device face. Dual-direction test and reset buttons. Class A rated GFCI. Supplied with matching TP26 nylon wall plate. Tri-drive screws.
Specifications	
<ul style="list-style-type: none"> Supply Voltage: 125VAC, 60 Hz Supply Voltage Range: 102-132 VAC Trip Threshold: 5± 1mA 	<ul style="list-style-type: none"> Trip Time: 0.025 sec., nominal per UL Standard 20 Amp feed-thru capacity



1595SWTTRWCC4

Catalog Number	Switch Rating A. VAC	Receptacle Rating A. VAC	Color	NEMA Config. No.	3rd Party Compliance		
					cUL ^{us} UL943 C22.2 No. 144	cUL ^{us} UL498 C22.2 No. 42	cUL ^{us} UL20 C22.2 No. 111
Combination Tamper-Resistant Single Pole Switch/GFCI							
1595SWTTRICC4	15 120	15 125	Ivory	5-15R	•	•	•
1595SWTTRWCC4	15 120	15 125	White	5-15R	•	•	•
1595SWTTRBKCC4	15 120	15 125	Black	5-15R	•	•	•
1595SWTTRLACC4	15 120	15 125	Light Almond	5-15R	•	•	•













NEMA
5-15R

Devices & Wall Plates Color Selection Chart



Pass & Seymour

Devices & Plastic Wall Plate Colors















					
Ivory	Light Almond	White	Green		
					
Black	Blue	Brown	Gray	Orange	Red

See specific device and wall plate catalog charts for particular color availabilities.

Metal Wall Plates

					
Metal Finish Aluminum	Brass (Brushed)	Polished Brass	Stainless Steel	Brushed Bronze	Chrome

Custom Metal Wall Plates Paint Finish Colors

						
Paint Color Orange	Green	Gray	Yellow	Glossy Black	Brown	White
						
Paint Color Primer	Red	Pink	Flat Black	Ivory	Light Almond	Blue

To order custom metal wall plates, see Pages Q-43 – Q-45.

For additional colors consult factory.