



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



16756 1/2" Hole-Hawg Drill 300/1200 RPM

Milwaukee Electric Tool

Catalog Number	16756
Manufacturer	Milwaukee Electric Tool
Description	Power and Torque, That'S About All That Needs to Be Said About The Hole-Haw Line Of Drills. The Compact Design Of This Drill Makes It Perfect For Drilling Between Studs and Joists. This Unit Will Handle Up to A 4-5/8 In. Selfeed Bit. An Extra Long Pipe Handle Helps You Control The Power. Features Two Speed Ranges, 1200 and 300 RPM, This Will Greatly Increase The Versatility Of This Drill. Hi-Torque and Hi-Speed Make This The Perfect Choice For The Heavy Duty User. Powerful 7.5 Amp Motor. Powerful, Yet Comp
Weight per unit	14.5 (lbs/each)
Product Category	Power Tools - Corded

Features

Chuck Capacity	1/2 in.
Cord Length	8.0
Switch Type	Trigger
Voltage	120.0

Material, Color, and Finish

Handle Material	Metal
Housing Material	Metal

Dimensions and Weight

Height	18.75
Length	7.0
Width	6.75



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

Description	1/2" HOLE-HAWG DRILL 300/1200 RPM
extra long description	MILW 1675-6 1/2 HOLE HAWG
Features	1675-6 1/2 in. Hole Hawg
Long Description	Power and torque, that's about all that needs to be said about the hole-haw line of drills. The compact design of this drill makes it perfect for drilling between studs and joists. This unit will handle up to a 4-5/8 in. Selfeed bit. An extra long pipe handle helps you control the power. Features two speed ranges, 1200 and 300 RPM, this will greatly increase the versatility of this drill. Hi-torque and hi-speed make this the perfect choice for the heavy duty user. Powerful 7.5 amp motor. Powerful, yet comp
Product Type	1/2 Hole Hawg
Special Features	Handles Up To 4-5/8 IN Selfeed Bit; Two Speed: 300 And 1200 RPM, Reversing; Powerful 7.5 AMP Motor; Powerful, Yet Compact For Large Hole Drilling Between Joists And Studs; Chuck Type: Keyed; Cord Type: 8 FT Fixed; Tool Weight: 11.500 LB; Spindle Lock: No; Metal Capacity: 1/2 IN Twist Bit; Spindle Size: 5/8-16 IN; Gear Train: Triple; Construction Type: Grounded; Length: 6-1/2 IN

Manufacturer Information

Brand	Milwaukee®
GTIN	00045242001767
Manufacturers Part Number	1675-6
UPC	045242001767

Taxonomies, Classifications, and Categories

Category Description	POWER TOOLS
Type	HEAVY DUTY

Packaging

Carton	1
Weight	14.6
Weight Per each	14.53

Uses, Certifications, and Standards

Application	For Large Hole Drilling Between Joists And Studs
-------------	--