



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 166G 2" Grounding Locknut Diecast

*Nsi Industries*

Catalog Number	166G
Manufacturer	Nsi Industries
Description	Locknut, Grounding, Zinc Die Cast, Size 2 Inch, 14-1/0 Lug
Weight per unit	0.3889 (lbs/each)
Product Category	Grounding & Bonding Equipment

### Features

Cable Entry	Through the fitting or conduit that the locknut is attached to
Material	Zinc Die Cast, Tin Plated Aluminum
media	Yes

### Material, Color, and Finish

Color	Gray
Finish	Ball burnish

### Dimensions and Weight

Size	2
------	---

### Descriptions

Description	2" GROUNDING LOCKNUT DIECAST
extra long description	BPT 166-G 2" GROUNDING L/N W/LUG
Features	Problem Solver: Connect and Ground with just a locknut!
Long Description	Locknut, Grounding, Zinc Die Cast, Size 2 Inch, 14-1/0 Lug
Product Type	2" Grounding L/N W/Lug
Special Features	Bridgeport's grounding locknuts provide a secure connection to the enclosure, and 3 tapped holes for proper placement of the ground lug.

### Manufacturer Information

Brand	Bridgeport Fittings
GTIN	00781747901668
Manufacturers Part Number	166G
UPC	781747901668

### Taxonomies, Classifications, and Categories

Category Description	SERVICE ENTRANCE FITTINGS: Weatherheads & Grounding Fittings & Ground Rods
Type	LOCKNUT

### Trade Size

Trade Size	2
------------	---



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	10
Package	50
Weight Per each	0.3889

## Uses, Certifications, and Standards

Application	Used in place where a grounding bushing and locknut, for bonding connectors inside the box. Perfect for tight locations or fittings with shorter locknut threads. ETL Listed for use with all Bridgeport Fittings connectors.
standard	Listed ETL Conforms to UL STD 514B Certified to CAN/CSA STD. C22.2 No. 18.3