

## 2-1/8" DEEP WITH NONMETALLIC CABLE CLAMPS

## Application

- Octagon boxes are used in the installation of ceiling or wall lighting fixtures
- Extension rings provide a means for adding additional cubic capacity or as an outlet box for surface conduit

## Product Features

- Reference Box Selection section in the front of this catalog for complete description of bracket and clamp types and features
- Combination screw heads provide for faster installation



175



176



177



128




130



131RAC

## 4" OCTAGON BOXES



## ORDERING INFORMATION - DIMENSIONS

## 4" OCTAGON BOX – 2-1/8" DEEP – DRAWN WITH NONMETALLIC SHEATHED CABLE CLAMPS – 21.5 CUBIC INCHES

| CATALOG NUMBER | DESCRIPTION BRACKET & SETBACK | KNOCKOUTS |        |        | STD. PKG. | UPC BAR CODE | RECOMMENDED MAX. SUPPORT LOADS |                       |
|----------------|-------------------------------|-----------|--------|--------|-----------|--------------|--------------------------------|-----------------------|
|                |                               | SIDES     |        | BOTTOM |           |              | CEILING FAN (DYNAMIC) LBS.     | FIXTURE (STATIC) LBS. |
|                |                               | CABLE     | COND.  | COND.  |           |              |                                |                       |
| 175            | —                             | 4         | 2-1/2" | 1-1/2" | 50        |              | No                             | 50                    |
| 176            | J brkt., 5/8"                 | 4         | 2-1/2" | 1-1/2" | 25        |              | No                             | 50                    |
| 177            | TS brkt., 1/2"                | 4         | 1-1/2" | 1-1/2" | 25        | —            | No                             | 50                    |

## 4" OCTAGON EXTENSION RINGS – 1-1/2" DEEP – DRAWN WITH CONDUIT KO'S – 15.5 CU. IN.

| CATALOG NUMBER | DESCRIPTION BRACKET & SETBACK | KNOCKOUTS SIDES COND. | STD. PKG. | UPC BAR CODE | RECOMMENDED MAX. SUPPORT LOADS |                       |
|----------------|-------------------------------|-----------------------|-----------|--------------|--------------------------------|-----------------------|
|                |                               |                       |           |              | CEILING FAN (DYNAMIC) LBS.     | FIXTURE (STATIC) LBS. |
|                |                               |                       |           |              |                                |                       |
| 128            | Extension ring                | 4-1/2"                | 25        |              | NO                             | 50                    |
| 130            | Extension ring                | 2-1/2", 2-3/4"        | 50        |              | NO                             | 50                    |
| 131RAC         | Extension ring                | 4-3/4"                | 25        |              | NO                             | 50                    |

## Compliance

- UL – File E195978
- CSA – File LR-1082 (128, 130, 131RAC)

## DIMENSIONS

| CATALOG NUMBER | A (INSIDE) | B  | C      | D    | E       | F      |
|----------------|------------|----|--------|------|---------|--------|
| 128            | 1-1/2"     | 4" | —      | —    | —       | —      |
| 130            | 1-1/2"     | 4" | —      | —    | —       | —      |
| 131RAC         | 1-1/2"     | 4" | —      | —    | —       | —      |
| 175            | 2-1/8"     | 4" | —      | —    | —       | —      |
| 176            | 2-1/8"     | 4" | 2-3/8" | 5/8" | —       | 3-1/8" |
| 177            | 2-1/8"     | 4" | 7"     | 1/2" | 1-1/16" | —      |