

Eaton 170M6760

Catalog Number: 170M6760

Fuse-link, high speed, 630 A, AC 690 V, size 3, 76 x 92 x 139 mm, aR, IEC, UL, single indicator

General specifications



Photo is representative

Product Name	Catalog Number
Eaton Bussmann series high speed square body fuse	170M6760
	UPC
	051712792752
EAN	Product Length/Depth
5996516020661	168 mm
Product Height	Product Width
76 mm	95 mm
Product Weight	Warranty
959 g	Not Applicable
Compliances	Certifications
CE Marked	IEC Rated
RoHS Compliant	UL Recognized

defaultTaxonomyAttributeLabel

Type

Fuse

Application

semiconductor protection

Amperage Rating

630 A

Breaking capacity

200 kA

Fuse indicator

Centre fuse status indicator

Insulated metal gripping lugs (IMGL)

No

Utilization category

aR (accompanied semiconductor protection)

Voltage type

AC

Fuse size

3

Rated voltage AC

690 V

Center-to-center distance of connections

114 mm

Current type

AC

Mounting dimension

Other

Class

Class aR

Clearing (I2T)

210000 at 660 V

Watt losses

105 W

Fuse shape

Square body, center bolted tags

Pre arc (I2T)

Resources

Catalogs

[eaton-product-overview-for-machinery-catalogue-ca08103003zen-en-us.pdf](#)

[170M6760-Eaton Bussmann series high speed square body fuse](#)

[Bussmann series complete full line catalog no. 1007](#)

31000

Color

None

Interrupt rating

200 kAIC

Fitted with:

Type K Indicator for micro

Connection

Blade end x blade end

Construction size

3

Packaging type

Standard

Voltage rating

690 V

Fuse type

US Style

FKE/115 Type K indicator for micro

Bolted tag

Fuse system (according to IEC 60269)

Other



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)