



PRODUCT DATA SHEET

Zinc-It® Instant Cold Galvanize, 13 Wt Oz
 No. 18412 | Item# 1005240 | Case# 1005239



Product Description	High-performance coating of >93% pure zinc that electrochemically bonds with ferrous metals to form a galvanic cell. It actively fights rust and corrosion. Use as a touch-up for damaged galvanized coatings. Dries quickly. Outdoor protection: 1-2 years.
Applications	On threads, exposed edges, fasteners, conduit, strapping, welds, fencing, railings, grates, electrical poles, breaker panel housings, rain spouts, signs, doors, trailers, waste containers, catwalks, and guard rails. Meets ASTM 780A
Unit Package Description	16 Ounce Aerosol
Brand	CRC
Generic Description 1	Instant Cold Galvanized Coating
Net Fill	13 Wt Oz
UPC Code	078254184128
Unit Dimensions	7.75H x 2.63W x 2.63D in
Units Per Case	12
Case Dimensions	8.69H x 8.44W x 11.31D in
Cases Per Pallet	75
Case Weight	14 lbs
I 2 of 5 Code	30078254184129
Appearance	Gray Viscous Liquid
Flash point (F)	-2°F
Flash point (C)	-19°C
Flammability Class - CPSC	Extremely Flammable
Spec Gravity Concentrate	0.77 to 0.85
Plastic Safe	Yes
Dry Time - Fully Dry	8 Hours
Dry Time - Tack Free	20 Minutes
Recoat	Before 1 Hour or After 48 Hours
Coverage	28 to 32 Sq Ft at 3 Mil Dry

Last revised: 6/29/2018
 Page 1 of 2



Customer Care: 800-556-5074
 Technical Assistance: 800-521-3168
www.crcindustries.com

CRC Industries is a worldwide leader in the production of specialty chemicals for maintenance and repair professionals serving industrial, electrical, aviation, automotive and marine markets. CRC is ISO 9001:2008 certified and adheres to the strictest guidelines for quality in all facets of research, development and production.



CRC®, K&W®, Sta-Lube®, Marykate® and products denoted with ® and ™ are trademarks of CRC Industries, Inc.



PRODUCT DATA SHEET



Working Temp (F)	130°F (Continuous) / 150°F (Intermittent)
Working Temp (C)	54.4°C (Continuous) / 65.6°C (Intermittent)
Propellant	Hydrocarbon
Aerosol Flammability Level	III
Military Specification Number	Meets requirements of Mil-P-26915, Meets requirements of Mil-P-46105, Meets requirements of Mil-P-21035B
DOT Proper Shipping Name	Aerosols, Flammable, Limited Quantity
VOC % (Consumer Product def)	45.6
VOC g/L (Consumer Product def)	555.6
VOC lbs/gal (Consumer Prod def)	4.64
VOC Category	Aerosol Coating: Metallic
MIR Limit (EPA)	1.9
MIR Limit (CA)	1.25
MIR Value	1.2
Removal (How To)	Remove with aromatic solvents, Xylene. Toluene can be used, but is not recommended.

Last revised: 6/29/2018
Page 2 of 2



Customer Care: 800-556-5074
Technical Assistance: 800-521-3168
www.crcindustries.com

CRC Industries is a worldwide leader in the production of specialty chemicals for maintenance and repair professionals serving industrial, electrical, aviation, automotive and marine markets. CRC is ISO 9001:2008 certified and adheres to the strictest guidelines for quality in all facets of research, development and production.



CRC®, K&W®, Sta-Lube®, Marykate® and products denoted with ® and ™ are trademarks of CRC Industries, Inc.



PRODUCT DATA SHEET

Zinc-It® Instant Cold Galvanize, 13 Wt Oz
 No. 18412 | Item# 1005240 | Case# 1005239



Product Description

High-performance coating of >93% pure zinc that electrochemically bonds with ferrous metals to form a galvanic cell. It actively fights rust and corrosion. Use as a touch-up for damaged galvanized coatings. Dries quickly. Outdoor protection: 1-2 years.

Applications

On threads, exposed edges, fasteners, conduit, strapping, welds, fencing, railings, grates, electrical poles, breaker panel housings, rain spouts, signs, doors, trailers, waste containers, catwalks, and guard rails. Meets ASTM 780A

Unit Package Description

16 Ounce Aerosol

Brand

CRC

Generic Description 1

Instant Cold Galvanized Coating

Net Fill

13 Wt Oz

UPC Code

078254184128

Unit Dimensions

7.75H x 2.63W x 2.63D in

Units Per Case

12

Case Dimensions

8.69H x 8.44W x 11.31D in

Cases Per Pallet

75

Case Weight

14 lbs

I 2 of 5 Code

30078254184129

Appearance

Gray Viscous Liquid

Flash point (F)

-2°F

Flash point (C)

-19°C

Flammability Class - CPSC

Extremely Flammable

Spec Gravity Concentrate

0.77 to 0.85

Plastic Safe

Yes

Dry Time - Fully Dry

8 Hours

Dry Time - Tack Free

20 Minutes

Recoat

Before 1 Hour or After 48 Hours

Coverage

28 to 32 Sq Ft at 3 Mil Dry

Last revised: 6/29/2018
 Page 1 of 2



Customer Care: 800-556-5074
 Technical Assistance: 800-521-3168
www.crcindustries.com

CRC Industries is a worldwide leader in the production of specialty chemicals for maintenance and repair professionals serving industrial, electrical, aviation, automotive and marine markets. CRC is ISO 9001:2008 certified and adheres to the strictest guidelines for quality in all facets of research, development and production.



CRC®, K&W®, Sta-Lube®, Marykate® and products denoted with ® and ™ are trademarks of CRC Industries, Inc.



PRODUCT DATA SHEET



Working Temp (F)	130°F (Continuous) / 150°F (Intermittent)
Working Temp (C)	54.4°C (Continuous) / 65.6°C (Intermittent)
Propellant	Hydrocarbon
Aerosol Flammability Level	III
Military Specification Number	Meets requirements of Mil-P-26915, Meets requirements of Mil-P-46105, Meets requirements of Mil-P-21035B
DOT Proper Shipping Name	Aerosols, Flammable, Limited Quantity
VOC % (Consumer Product def)	45.6
VOC g/L (Consumer Product def)	555.6
VOC lbs/gal (Consumer Prod def)	4.64
VOC Category	Aerosol Coating: Metallic
MIR Limit (EPA)	1.9
MIR Limit (CA)	1.25
MIR Value	1.2
Removal (How To)	Remove with aromatic solvents, Xylene. Toluene can be used, but is not recommended.

Last revised: 6/29/2018
Page 2 of 2



Customer Care: 800-556-5074
Technical Assistance: 800-521-3168
www.crcindustries.com

CRC Industries is a worldwide leader in the production of specialty chemicals for maintenance and repair professionals serving industrial, electrical, aviation, automotive and marine markets. CRC is ISO 9001:2008 certified and adheres to the strictest guidelines for quality in all facets of research, development and production.



CRC®, K&W®, Sta-Lube®, Marykate® and products denoted with ® and ™ are trademarks of CRC Industries, Inc.