



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



2097HGTRW Self-Test Gfci Rec Hosp Tamp Res 20A WH

Pass & Seymour/Legrand

Catalog Number	2097HGTRW
Manufacturer	Pass & Seymour/Legrand
Description	20A 125V Self Test Gfci Hospital Grade Tamper Resistant White
Weight per unit	0.2750 (lbs/each)
Product Category	Gen Purpose Recept & Surge Pro

Features

actuator	Control Circuit
amperage rating	20
connection	Back and side wire
interrupt rating	4 to 6 mA
Material	Thermoplastic
Poles	2
trip range	4 to 6 mA
Trip Type	.025 Second Nominal
Voltage Rating	125

Dimensions and Weight

Height	4.2
Length	1.03
Width	1.73

Descriptions

Description	SELF-TEST GFCI REC HOSP TAMP RES 20A WH
extra long description	P&S 2097HGTRW SELF-TEST GFCI REC HO
Long Description	20A 125V Self Test GFCI Hospital Grade Tamper Resistant White
Product Type	Self-Test Gfci Rec Hosp Tamp Res 20A WH
Special Features	Pass & Seymour invented the GFCI receptacle, and at Legrand, we're constantly reinventing it to ensure the highest level of safety possible. From the most advanced self-testing device to audible alarms to nightlight combos, we're continuously resetting the bar on GFCI innovation and safety.

Manufacturer Information

Brand	LEGRAND-PASS & SEYMOUR
GTIN	00785007035940
Manufacturers Part Number	2097HGTRW
UPC	785007035940

Taxonomies, Classifications, and Categories

Category Description	Residential Switches
Type	Hospital-Grade Tamper-Resistant 20A Self-Test Duplex GFCI



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Package	10
Weight Per each	0.275

Uses, Certifications, and Standards

Application	Commercial/Residential
environmental conditions	95% Humidity, UL 94 V2
Frequency Rating	60 Hz
Operating Temperature	-35°C to +66°C
standard	cULus, UL Listed, FSUL