



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



2097TRWRW Radiant Self Test TR WR GFI 20A 125V WH

Pass & Seymour/Legrand

| | |
|------------------|--|
| Catalog Number | 2097TRWRW |
| Manufacturer | Pass & Seymour/Legrand |
| Description | Self-Test Duplex Receptacle, 20 A, 125 V, 2 Poles, #14 to #10 Awg Compatible Wire Size, Control Circuit Actuator, Back and Side Wired Connection, 60 HZ, 1.73 In Width, 4.20 In Height, Thermoplastic Material, White, 0.025 Sec Trip Time, Weather Resistant, 0.2800 LB |
| Weight per unit | 0.2750 (lbs/each) |
| Product Category | Gen Purpose Recept & Surge Pro |

Features

| | |
|------------------|---------------------|
| actuator | Control Circuit |
| amperage rating | 20 |
| connection | Back and side wire |
| interrupt rating | 4 to 6 mA |
| Poles | 2 |
| trip range | 4 to 6 mA |
| Trip Type | .025 Second Nominal |
| Voltage Rating | 125 |

Dimensions and Weight

| | |
|--------|------|
| Length | 1.03 |
| Width | 1.73 |

Descriptions

| | |
|------------------------|---|
| Description | RADIANT SELF TEST TR WR GFI 20A 125V WH |
| extra long description | P&S 2097TRWRW RADIANT SELF TEST TR |

Manufacturer Information

| | |
|-------|----------------|
| Brand | Pass & Seymour |
| GTIN | 00785007036107 |
| UPC | 785007036107 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|---|
| Category Description | Residential GFCI devices |
| Type | Specification Grade Weather-Resistant 20A Self-Test Duplex GFCI |

Packaging

| | |
|-----------------|-------|
| Carton | 1 |
| Package | 10 |
| Weight Per each | 0.275 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

| | |
|--------------------------|------------------------|
| environmental conditions | 95% Humidity, UL 94 V2 |
| Operating Temperature | -35°C to +66°C |
| standard | cULus, UL Listed, FSUL |