



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



2116 277V 2000W D/C ZNC PHCTRL

Nsi Industries

| | |
|------------------|-------------------------------------|
| Catalog Number | 2116 |
| Manufacturer | Nsi Industries |
| Description | Tork 2116 Photocontrol Stem Aluminu |
| Weight per unit | 0.5100 (lbs/each) |
| Product Category | Lighting |

Features

| | |
|----------------|-----------|
| supply voltage | 120 Vac |
| Timing Range | 2 Minutes |

Dimensions and Weight

| | |
|------|--------------------|
| Size | .500 Conduit Mount |
|------|--------------------|

Descriptions

| | |
|------------------|--|
| Description | 277V 2000W D/C ZNC PHCTRL |
| Long Description | TORK 2116 Photocontrol Stem Aluminu |
| Product Type | Photocontrol Stem Aluminum 240V |
| Special Features | 1/2 Conduit Mount - Time Delay On And Off - Cadmium Sulphide Epoxy Coated 1/2 Diameter Cell |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | NSi |
| GTIN | 00786261600332 |
| Manufacturers Part Number | 2116 |
| UPC | 786261600332 |

Taxonomies, Classifications, and Categories

| | |
|------|--------------------------------|
| Type | Die Cast Aluminum Photocontrol |
|------|--------------------------------|

Availability

| | |
|---------------------|----------|
| Manufacturer Status | Inactive |
| Status | Inactive |

Packaging

| | |
|-----------------|------|
| Carton | 1 |
| Weight Per each | 0.51 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

| | |
|--------------------------|---|
| Application | Parking Lot-Building Perimeter-Outdoor Signage Lighting |
| Enclosure | Aluminum Diecast |
| environmental conditions | -40 to + 140 F |
| Frequency Rating | 50-60 Hz |
| Mounting | Conduit Mount |
| Operating Temperature | -40 to + 140 F |
| standard | cULus |