



MAGNATEC® PREMIUM DETECTABLE TAPE 1000' x 3"

Use for location and early warning protection for underground lines
Middle foil layer allows for both inductive and conductive locating

INCLUDES:

[\(1\) MAGNATEC® PREMIUM DETECTABLE TAPE \(31-150\)](#)

FEATURES:

- Environmentally safe
- Lead free
- Maximum strength
- Permanent messaging

PRODUCT SPECIFICATIONS:

| Feature | Method | Value (English) | Value (SI) |
|-------------------|---------------|----------------------------------|------------------------------|
| Overall Thickness | ASTM D-2103 | 5.0 mil (Nominal) | 0.125 mm |
| Foil Thickness | ASTM D-2103 | .35 mil | 8.89 microns |
| Weight | ASTM D-2103 | 27.5 lbs / 1,000 ft ² | 13.4 kg / 100 m ² |
| Tensile Strength | ASTM D-882 | Length: 7,651 psi | Length: 52.8 Mpa |
| Elongation | ASTM D-882 | Length: 89% | Length: 89% |
| Printability | ASTM D-2578 | | > 40 dynes |
| Plastic Density | ASTM D-792-08 | | 1.119 g/cc |



**MAGNATEC® PREMIUM
DETECTABLE TAPE 1000' x 3"**

Use for location and early warning protection for underground lines
Middle foil layer allows for both inductive and conductive locating

INCLUDES:

- [\(1\) MAGNATEC® PREMIUM DETECTABLE TAPE \(31-150\)](#)

FEATURES:

- Environmentally safe
- Lead free
- Maximum strength
- Permanent messaging

PRODUCT SPECIFICATIONS:

| Feature | Method | Value (English) | Value (SI) |
|-------------------|---------------|----------------------------------|------------------------------|
| Overall Thickness | ASTM D-2103 | 5.0 mil (Nominal) | 0.125 mm |
| Foil Thickness | ASTM D-2103 | .35 mil | 8.89 microns |
| Weight | ASTM D-2103 | 27.5 lbs / 1,000 ft ² | 13.4 kg / 100 m ² |
| Tensile Strength | ASTM D-882 | Length: 7,651 psi | Length: 52.8 Mpa |
| Elongation | ASTM D-882 | Length: 89% | Length: 89% |
| Printability | ASTM D-2578 | | > 40 dynes |
| Plastic Density | ASTM D-792-08 | | 1.119 g/cc |