



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 30T 3/0 Al/Cu 1 Conductor Mechanical Lug

*Nsi Industries*

|                  |   |
|------------------|---|
| Catalog Number   | 30T   |
| Manufacturer     | Nsi Industries  |
| Description      | Mechanical Connector, #6 Awg Conductor Size, 3/0 Awg Conductor Size, Non-Insulated, Aluminum/Copper Conductor Material, 1 Conductor, +90 °C Operating Temperature, 1.875 In Overall Length, Screw Terminal, 600 V, 0.05 LB/Ea |
| Weight per unit  | 0.0500 (lbs/each)   |
| Product Category | Large Terminals & Connectors  |

### Features

|                |        |
|----------------|--------|
| Voltage Rating | 600    |
| Warranty       | 1 YEAR |

### Descriptions

|                        |   |
|------------------------|---|
| Description            | 3/0 AL/CU 1 CONDUCTOR MECHANICAL LUG  |
| extra long description | NSI 3/0T RG6 Cable Clip. 100/Bag.   |
| Features               | 1 Port Aluminum Lug 3/0-6 AWG Aluminum Single Lugs are versatile and feature reuseable set screw connectors made of 6061T-6 aluminum alloy. Electro-tin plated for low contact resistance. Suitable for use with both copper and aluminum conductors. Temperature Rating 90 degrees C. Rated 600 volts (2000V max. per UL486B). UL 486A/B Listed. . |

### Manufacturer Information

|       |                |
|-------|----------------|
| Brand | Platinum Tools |
| GTIN  | 00662381001054 |
| UPC   | 662381001054   |

### Taxonomies, Classifications, and Categories

|                      |                     |
|----------------------|---------------------|
| Category Description | SPLIT BOLTS         |
| Type                 | Aluminum Single Lug |

### Packaging

|                 |      |
|-----------------|------|
| Carton          | 1    |
| Package         | 50   |
| Weight Per each | 0.05 |

### Uses, Certifications, and Standards

|             |                  |
|-------------|------------------|
| Application | Wire Termination |
| standard    | UL486A/B         |